

PHILIPS

Coffee maker

Pure Essentials


With glass jug

Made in Germany

Black



HD7686/90



Have it your way, exactly your way

My Aroma Control for personal strength setting

This sophisticated Philips coffee maker combines excellent quality in aroma and in design. The strength control feature allows you to brew your filter coffee to your personal liking, thanks to the integrated coffee scale.

Great taste and aroma

- 1400 Watt

Designed around you

- Strength select for adjusting the intensity of your coffee
- Decalcification indicator light

Easy to experience

- Drip stop to pour a cup of coffee whenever you like
- Auto shut-off after 2 hours
- Swing filter holder for easy filling of coffee
- Detachable water tank for easy filling
- Cable storage for easy placement in your kitchen
- Dishwasher proof parts for easy cleaning

Highlights

Strength select

Adjust the intensity of your coffee to mild, medium or intense coffee.

Decalcification indicator

The Philips coffee machine will remind you when to descale your appliance. Regular descaling ensures your coffee tastes its best and prevents build-up of limescale from tap water.

Drip stop




The drip stop allows you to pour a cup of coffee before the full brewing cycle is finished.

Auto shut-off



Forgotten to turn off the coffee machine? Don't worry! 2 hours after brewing the coffee, the coffee machine will shut off automatically to save energy.

Detachable water tank



The water tank is detachable, which makes it easy to fill up with water or clean the water tank.

Specifications

Design

Colour: Black

Your filter coffee your way

Automatic switch-off

Good filter coffee made easily

Water level indication

Detachable filter holder

Dishwasher-safe parts

Drip stop

Illuminated power switch

Weight and dimensions

Product dimensions (L x D x H): 382 x 196 x 395 mm

Water tank capacity: 1.2 l

Packaging weight: 2.7 kg

Product weight: 2 kg

General specifications

Ease of cleaning and maintenance:

Dishwasher-safe parts

Technical specifications

Coffee jug type: Glass aroma jug

Cord storage

Supported coffee types: Ground coffee

Country of origin: Made in China, Designed in the Netherlands

Power: 1400 W

Voltage: 220-240 V

Frequency: 50/60 Hz

Brewing time: < 10 minute(s)

Capacity: 1.2 l / 10-15 cups

Cord length: 88 cm

Design specifications

Colour(s): HD 7686/90 Black/stainless steel/red accents

Accessories

Included: Glass jug

Jug: HD7985 (white), HD7986 (black)

