

PHILIPS

Coffee maker

Pure Essentials

With thermal jug

Made in Germany

Black

HD7692/90



Have a perfect espresso just pressing a button My Aroma Control for personal strength setting

This sophisticated coffeemaker combines excellent quality in aroma with great design. The strength control feature allows you to brew your coffee to your taste whenever you want, the insulated jug keeps your coffee fresh and hot for longer.

Great taste and aroma

- 1.400 Watt
- Unbreakable stainless steel insulated jug

Designed around you

- Strength select for adjusting the intensity of your coffee
- Decalcification indicator light

Easy to experience

- Drip stop to pour a cup of coffee whenever you like
- Direct automatic shut-off for energy saving and safety
- Detachable water tank for easy filling
- Swing filter holder for easy filling of coffee
- Cable storage for easy placement in your kitchen

Highlights

Strength select

Adjust the intensity of your coffee from mild, medium or intense coffee.

Decalcification indicator


The Philips coffee machine will remind you when to descale your appliance. Regular descaling ensures the best taste of your coffee and prevents lime scale from tap water.

Drip stop



The drip stop allows you to pour a cup of coffee before the full brewing cycle is finished.


Direct automatic shut-off



Auto-off

After brewing your coffee, the coffeemaker switches off automatically for energy saving and safety. The thermal jug will ensure that the coffee stays hot.

Detachable water tank



The water tank is detachable, which makes it easy to fill water or clean the water tank.

Insulated Jug



The unbreakable stainless steel insulated jug of this Philips coffee machine maintains perfect temperature and aroma for hours.

Specifications

Design

Color: Black

Your filter coffee your way

Automatic switch-off

Good filter coffee made easily

Water level indication

Detachable filter holder

Dishwasher safe parts

Drip stop

Illuminated power switch

Weight and dimensions

Product dimensions (L x D x H): 382 x 196 x 395 mm

Water tank capacity: 1.2 L

Packaging weight: 3.2 kg

Product weight: 2.7 kg

Technical specifications

Coffee jug type: Unbreakable thermal jug,

Glas aroma jug

Cord storage

Supported coffee types: Ground coffee

Country of origin: Made in China, Designed in the Netherlands

Power: 1400 W

Voltage: 220-240 V

Frequency: 50/60 Hz

Brewing time: < 10 minute(s)

Capacity: 1.2 L / 10-15 cups

Cord length: 88 cm

Design specifications

Color(s): HD 7692/90 Black/stainless steel/red accents

