

PHILIPS

Coffee maker

Intense

With glass jug

With intensity switch

Black & metal

HD7695/90



Have it your way, exactly your way

Mild to intense coffee with the intensity switch

The patented intensity switch lets you set the way the water flows through the coffeebed: a wide water distribution setting gives a smooth, mild taste, while a narrow distribution results in a strong, intense taste.

Great taste and aroma

- Aroma twister circulates the coffee for an optimal taste
- Intensity switch to brew from mild to strong coffee
- Freshness indicator

Easy to experience

- Drip stop to pour a cup of coffee whenever you like
- Detachable water tank for easy filling
- Adjustable keep-warm time from 10 minutes to 2 hours
- Calc clean setting for optimal decalcification
- Dishwasher-safe parts for easy cleaning
- Auto shut-off after 30 min. for energy saving and safety

Highlights

Aroma twister



This smart nozzle inside the jug circulates the inflowing coffee evenly through the jug for an optimal and consistent aroma, from the first to the last cup.

Intensity switch



The patented intensity switch lets you set the way the water flows through the coffeebed: a wide water distribution setting gives a smooth, mild taste, while a narrow distribution results in a strong, intense taste.

Drip stop



The drip stop allows you to pour a cup of coffee before the full brewing cycle is finished.

Adjustable keep-warm time



Select how long you want your coffee to stay hot after brewing. You can adjust the automatic shut-off time from 10 minutes up to 2 hours.

Freshness indicator



The freshness indicator shows when your coffee does not have its optimal aroma and freshness anymore.

Detachable water tank




The water tank is detachable, which makes it easy to fill water or clean the water tank.

Calc clean setting



The special calc clear setting ensures an optimal result when you descale the coffee maker. This is important for maintaining a delicious coffee taste.

Dishwasher-safe parts



The jug and filter holder can be easily cleaned in the dishwasher.

Automatic shut-off (30 min)



Auto-off

30 Minutes after brewing your coffee, the coffeemaker switches off automatically for energy saving and safety. This is according to EU regulation, which is applicable for all coffee makers in the EU. If you want your coffee to stay hot longer, Philips offers coffee makers with a thermal jug.

Specifications

Country of origin

Made in: China

Sustainability

Power consumption brewing: 1000 W

Weight and dimensions

Dimensions of product (WxDxH): 228 x 387 x 410 mm

Weight of product: 1.895 kg

Dimensions of packaging (WxDxH): 288 x 420 x 490 mm

Weight incl. packaging: 2.495 kg

Service

2-year guarantee

Finishing

Material water tank: Plastic

Material of main body: Stainless steel & plastic

Design

Color: Black & Metal

General specifications

Temperature settings: 3

Coffee drinks: Drip filter coffee

Suitable for: Ground coffee powder

Customizing per drink: Adjustable coffee strength, Adjustable temperature

Ease of use and comfort: Removable water tank, Water level indication, Automatic shut-off, Drip stop

Ease of cleaning & maintenance: Descale indicator, Removable filter holder, Dishwasher-safe parts

Special functions: Intensity Switch

Accessories

Included: Glass jug

Technical specifications

Capacity water tank: Up to 15 cups

Brewing time for a jug: 10 min

Capacity water tank: 1.2 L

Cord length: 0.88 m

Voltage: 220 - 240 V

Frequency: 50 - 60 Hz

