




SENSEO® Viva Café
Coffee pod machine

- New Generation
- Raven black



HD7820/69

Experience the world of coffee with SENSEO® New Generation

Make your coffee moments special with SENSEO®. This unique system combines the easy-to-use SENSEO® coffee machine with the specially developed Douwe Egberts SENSEO® coffee pods, giving you a full, smooth coffee with a delicious foam layer.

Ultimate convenience

- 1 or 2 cups of SENSEO® coffee in less than a minute
- Adjustable spout to fit your favorite cup
- Removable extra-large water reservoir for fewer refills
- Automatic shut-off for less energy consumption

Sensational coffee

- Delicious coffee foam layer for your special coffee moment
- Large coffee pod variety to accommodate choice



* Based on retail sales volumes

Senseo®

PHILIPS

Highlights

Two cups in less than a minute



With the SENSEO® coffeemaker you can have your perfect cup of delicious, freshly brewed coffee in approximately 30 seconds and two cups in less than a minute.

Delicious coffee foam layer



The fine Douwe Egberts SENSEO® coffee selection and the unique SENSEO® brewing system make sure that your perfect cup of coffee always comes with a rich and delicious coffee foam layer - proof of premium taste and quality.

Adjustable spout



By raising or lowering the spout you can adjust your SENSEO® coffee machine to the size of your favorite cup or mug.

Extra-large water reservoir



The removable extra-large water reservoir of the coffeemaker has the capacity to accommodate 8 cups of coffee and therefore minimizes coffee preparation time.

Large coffee pod variety



With more than 250 years of experience, Douwe Egberts knows exactly how to roast and grind carefully selected coffee beans for the best taste. Therefore Douwe Egberts SENSEO® coffee pod varieties represent the finest coffee selection as a guarantee for premium taste. The different blends and flavors ensure a wide range of choice for different moments and tastes.

Specifications

Design

- Color: Deep Black

Finishing

- Material of main body: Plastic

Country of origin

- Made in: Poland

General specifications

- Ease of use and comfort: Automatic shut-off

Technical specifications

- Frequency: 50 Hz
- Capacity water tank: 1.2 L
- Capacity water tank: Up to 8 cups
- Cord length: 0.8 m
- Max. cup height: 97 - 117 mm
- Power: 1450 W
- Voltage: 220-240 V

Weight and dimensions

- Dimensions of product (WxDxH): 190 x 310 x 340 mm
- Weight of product: 2.4 kg

