



**SENSEO® Viva Café**  
Coffee pod machine

- Adjustable metal spout
- Deep Black
- Direct start



HD7825/60

## Delicious coffee at the touch of a button

Adjustable metal spout to fit your favourite cup

Enrich your coffee moments with SENSEO® Viva Café coffee machine. The wide range of features, like the choice to make one or two cups of coffee at the same time, adjustable real metal spout and direct start, ensure the ultimate convenience.

### Always a delicious cup of coffee

- Delicious coffee crema layer as proof of SENSEO® quality
- Unique brewing system for optimal taste and temperature
- Machine is tested > 10,000 times to ensure consistent quality

### Coffee variety for every moment

- Variety of coffee blends and flavours for different tastes

### Fast and easy operation

- Unique coffee machine that brews 2 cups at a time
- Adjustable real metal spout to fit your favourite cup
- Direct start to select your coffee while machine heats up
- 30 minutes auto shut-off for energy saving and safety
- The decalcifying light reminds you when to descale



\* Based on retail sales volumes

*Senseo*

**PHILIPS**

Coffee pod machine  
Adjustable metal spout Deep Black, Direct start

HD7825/60

## Highlights

### Delicious coffee crema layer



The fine SENSEO® coffee selection and the unique SENSEO® brewing system make sure that your perfect cup of coffee always comes with a rich and delicious coffee foam layer - proof of premium taste and quality.

### Decalcification indicator



The SENSEO® coffee machine reminds you when to descale. Descale with the specially developed SENSEO® descaler to ensure the best coffee taste and prevent limescale from tap water.

### Adjustable real metal spout



By raising or lowering the spout of your SENSEO® Viva Café, you can adjust it to fit your favourite cup or mug.

### Variety of blends and flavours



SENSEO® offers you a large variety of coffee blends and flavours, each with its own distinctive taste to fit your personal preference.

### 1 or 2 cups at the same time



This SENSEO® coffee maker prepares one or two cups of your delicious SENSEO® coffee in less than a minute.

### Automatic shut-off



Your SENSEO® coffee machine automatically switches off after 30 minutes, allowing you to save energy.

## Specifications

### General specifications

- Cups at the same time: 2
- Compatible coffee serving: SENSEO® Coffee pods
- Customise each drink: Memo function cup volume
- Ease of use and comfort: Removable water tank, Adjustable spout, Removable drip tray, Automatic shut-off, Brew stop, Direct start
- Ease of cleaning and maintenance: Dishwasher-safe parts, Descale indicator
- Coffee drinks: Café Crème

### Finishing

- Material boiler: Metal and glass-filled polyamide
- Material drip tray: Metal
- Material of main body: Plastic
- Material of spout: Stainless steel
- Material water tank: Plastic

### Country of origin

- Made in: Poland

### Sustainability

- Power consumption stand-by: 0.36 W
- Power consumption brewing: 1450 W
- Sustainability certification: Green tick
- Made of recycled materials: 90% (paperwork and packaging)

### Service

- 2 year guarantee

### Technical specifications

- Pump pressure: 1 bar
- Capacity water tank: Up to 6 cups
- Max. cup height: 100 - 120 mm
- Brewing time one cup: 30 sec
- Water boilers: 1
- Brewing time two cups: < 60 sec
- Cord length: 0.8 m
- Capacity water tank: 0.9 l
- Frequency: 50 Hz
- Voltage: 220 - 240 V

### Weight and dimensions

- Weight of product: 1.75 kg
- Weight incl. packaging: 2.4 kg
- Dimensions of product (W x D x H): 190 x 310 x 340 mm
- Dimensions of packaging (W x D x H): 232 x 370 x 380 mm

Issue date 2019-11-28

© 2019 Koninklijke Philips N.V.  
All Rights reserved.

Version: 18.2.1

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)



[asimpleswitch.com](http://asimpleswitch.com)