




SENSEO®  
Coffee pod system

• Latte Select



HD7850/60

## Experience your favourite coffee specialties

### with SENSEO® Latte Select

The SENSEO® Latte Select coffee machine offers you delicious coffee specialties made with fresh frothed milk. Choose from Cappuccino, Latte Macchiato, Café Latte and normal black SENSEO® coffee - all at the touch of a button.

#### Sensational coffee

- Unique brewing system for optimal taste
- Volume Select option to customise and optimise coffee volume
- Delicious coffee foam layer for your special coffee moment
- Large coffee pod variety to accommodate choice

#### Coffee specialties with fresh, frothed milk

- Automatic frothing system for perfectly frothed milk
- Coffee specialties with a perfect balance of coffee and milk
- Dual heating system instantly warms up coffee and milk

#### Ultimate convenience

- 1 or 2 cups at a time
- Easy-clean button for comfortable cleaning
- Adjustable cup tray accommodates different cup sizes
- Integrated, removable milk container for more convenience



\* Based on retail sales volumes

Senseo®

PHILIPS

# Highlights

## Unique brewing system



Unique SENSEO® coffee brewing system from Philips and Douwe Egberts. Every cup is freshly brewed and prepared with the ultimate balance between coffee and water - a guarantee for a smooth, full taste and delicious aroma.

## Automatic frothing system



The automatic frothing system of your SENSEO® Latte Select coffee machine allows you to prepare various coffee specialties with freshly frothed milk with a rich foam layer

## Volume select



The Volume Select function allows you to choose the desired amount of either black or specialty coffee.

## Delicious coffee foam layer



The fine Douwe Egberts SENSEO® coffee selection and the unique SENSEO® brewing system make sure that your perfect cup of coffee always comes with a rich and delicious coffee foam layer - proof of premium taste and quality.

## Large coffee pod variety



With more than 250 years of experience, Douwe Egberts knows exactly how to roast and grind carefully selected coffee beans for the best taste. Therefore Douwe Egberts SENSEO® coffee pod varieties represent the finest coffee selection as a guarantee for premium taste. The different blends and flavours ensure a wide range of choice for different moments and tastes.

## Easy-clean function



With the Easy-Clean function you can remove milk residues from your machine in a fast and comfortable way. It also indicates when cleaning or decalcification is required.

## Removable fresh milk container

The removable fresh milk container allows quick refills and easy cleaning

# Specifications

## Technical specifications

- Power: 2650 W
- Voltage: 220-240 V
- Frequency: 50–60 Hz
- Cord length: 100 cm
- Water tank capacity: 1.2/8 Litres/cups
- Auto-off: 30 minute(s)
- Spout height: 97-133 mm
- Black coffee brew volume: 80/120/150 ml
- Cappuccino brew volume: 160 ml
- Café Latte brew volume: 190 ml
- Latte Macchiato brew volume: 220 ml

## Design specifications

- Materials: Plastic
- Colour(s): Deep Black

## Country of origin

- Country of origin: Poland

## Dimensions

- Dimensions (W x H x D): 205 x 350 x 350 mm
- Packaging dimensions (WxHxD): 232 x 399 x 390 mm