



SENSEO® Latte Duo
Coffee pod machine

- 2 cappuccinos in one go
- Integrated milk frother
- Easy-clean function



HD7855/50

Finally two cappuccinos in one go from fresh milk!

SENSEO® coffee variety: six recipes

Unlimited choice with the SENSEO® Latte Duo coffee machine: cappuccino, latte macchiato, latte, strong or mild coffee. Also you can prepare fresh frothed milk for your kids. And this is as fast as can be with 2 cups.

Coffee specialties made with fresh frothed milk

- Only SENSEO® Latte Duo serves 2 milk drinks at a time
- Enjoy 4 coffee & milk recipes at one touch of a button
- Firm hot milk froth thanks to patented frothing system

Coffee variety for every moment

- Select your coffee strength: strong short or mild long
- Delicious coffee crema layer as proof of SENSEO® quality
- Machine is tested >10.000 times to ensure consistent quality
- Variety of coffee blends and flavors for different tastes

Easy to clean and fast operation

- Easy clean milk frothing system & descaling program
- Milk frother will draw milk directly from a carton or jug
- Adjustable tray to fit your favorite cup
- Intuitive controls for smart guided operation



Senseo

PHILIPS

* Based on retail sales volumes

Highlights

2 milk drinks at a time



Save time and effort with the patented Duo Latte function in your SENSEO® Latte Duo coffee maker. Make 2 cups of any coffee specialty you like at the same time at the touch of only one button. Enjoy making your coffee specialty preparation as easy and effortless as never before.

Fresh milk coffee specialties



Enjoy your delicious SENSEO® cappuccino, latte macchiato or café latte with a rich combination of coffee and fresh milk. Each cup is crowned with a creamy foam layer, just like the ones you can enjoy in coffee bars!

Hot, creamy milk froth



SENSEO®'s patented frothing system uses state-of-the-art technology for excellent performance, delivering a perfect, hot milk specialty every time.

Strength select function



Prepare your favorite cup of coffee by adjusting the strength and intensity of its taste. With the strength select function on your SENSEO®, you can choose between strong short and mild long coffee.


Delicious coffee crema layer



The fine SENSEO® coffee selection and the unique SENSEO® brewing system make sure

that your perfect cup of coffee always comes with a rich and delicious coffee foam layer - proof of premium taste and quality.

Easy clean system



All parts in your Philips SENSEO® Latte Duo coffee maker that get in touch with milk can be cleaned thoroughly, through the One-Touch cleaning routine after each use. Or simply disassemble the milk spout and wash all parts thoroughly by hand or in the dishwasher at the end of the day. The machine also will remind you when to descale your appliance.

Easy milk frother



Enjoy super creamy cappuccinos at the perfect temperature, in the easiest way possible. Simply use your milk carton or pour milk into a carafe, place the milk tube, and select your preferred beverage. Whether it's a cappuccino or frothed milk, your drink will be served within seconds, with a splash-free flow at the ideal temperature.

Specifications

Country of origin

- Made in: Poland

General specifications

- Special functions: Automatic milk frother
- Coffee drinks: Café Crème, Café Latte, Cappuccino
- Suitable for: SENSEO® Coffee pods
- Cups at the same time: 2
- Coffee strength settings: Strong, regular
- Customizing per drink: Adjustable coffee strength
- Ease of use and comfort: Removable spout, Direct start, Removable drip-tray, Removable water tank, Automatic shut-off
- Ease of cleaning & maintenance: Automatic descaling cycle, Easy-clean function, Descale indicator, Dishwasher-safe parts

Finishing

- Material drip tray: Plastic
- Material boiler: Metal & glass-filled polyamide
- Material water tank: Plastic
- Material of main body: Plastic
- Material of spout: chromed plastic

Sustainability

- Power consumption stand-by: 0.26 W
- Power consumption brewing: 2650 W
- Packaging: > 90% recycled materials

Service

- 2-year guarantee

Technical specifications

- Water boilers: 1
- Brewing time two cups: 75 sec
- Brewing time one cup: 45 sec
- Capacity water tank: 1 L
- Max. cup height: 85 - 135 mm
- Cord length: 0.8 m
- Frequency: 50 Hz
- Voltage: 230 V
- Pump pressure: 1 bar

Weight and dimensions

- Dimensions of product (WxDxH): 217 x 280 x 290 mm
- Weight of product: 2.4 kg

Design

- Color: Black