

PHILIPS

Coffee pod machine

Latte Duo Plus

2 cappuccinos in one go

Integrated milk frother

Easy-clean function

Black



HD7856/50



Finally two cappuccinos in one go from fresh milk!

SENSEO[®] coffee variety: six recipes

Unlimited choice with the SENSEO[®] Latte Duo coffee machine: cappuccino, latte macchiato, latte, strong or mild coffee. Also you can prepare fresh frothed milk for your kids. And this is as fast as can be with 2 cups in one go.

Coffee specialties made with fresh frothed milk

- Only SENSEO[®] Latte Duo serves 2 milk drinks at a time
- Enjoy 4 coffee & milk recipes at one touch of a button
- Firm hot milk froth thanks to patented frothing system

Coffee variety for every moment

- Select your coffee strength: strong short or mild long
- Delicious coffee crema layer as proof of SENSEO[®] quality
- Machine is tested >10.000 times to ensure consistent quality
- Variety of coffee blends and flavors for different tastes

Easy to clean and fast operation

- Easy clean milk frothing system & descaling program
- Milk frother will draw milk directly from a carton or jug
- Adjustable tray to fit your favorite cup
- Intuitive controls for smart guided operation

Highlights

2 milk drinks at a time



Save time and effort with the patented Duo Latte function in your SENSEO® Latte Duo coffee maker. Make 2 cups of any coffee specialty you like at the same time at the touch of only one button. Enjoy making your coffee specialty preparation as easy and effortless as never before.

Fresh milk coffee specialties



Enjoy your delicious SENSEO® cappuccino, latte macchiato or café latte with a rich combination of coffee and fresh milk. Each cup is crowned with a creamy foam layer, just like the ones you can enjoy in coffee bars!

Hot, creamy milk froth



SENSEO®'s patented frothing system uses state-of-the-art technology for excellent performance, delivering a perfect, hot milk specialty every time.

Strength select function




Prepare your favorite cup of coffee by adjusting the strength and intensity of its taste. With the strength select function on your SENSEO®, you can choose between strong short and mild long coffee.

Delicious coffee crema layer



The fine SENSEO® coffee selection and the unique SENSEO® brewing system make sure that your perfect cup of coffee always comes with a rich and delicious coffee foam layer - proof of premium taste and quality.

Easy clean system



All parts in your Philips SENSEO® Latte Duo coffee maker that get in touch with milk can be cleaned thoroughly, through the One-Touch cleaning routine after each use. Or simply disassemble the milk spout and wash all parts thoroughly by hand or in the dishwasher at the end of the day. The machine also will remind you when to descale your appliance.

Easy milk frother



Enjoy super creamy cappuccinos at the perfect temperature, in the easiest way possible. Simply use your milk carton or pour milk into a carafe, place the milk tube, and select your preferred beverage. Whether it's a cappuccino or frothed milk, your drink will be served within seconds, with a splash-free flow at the ideal temperature.

Adjustable drip tray



By raising or lowering the drip tray you can adjust your Philips SENSEO® coffeemaker to the size of your favorite cup or mug.

Smart guided controls



Operate your Philips coffeemaker in a modern and intuitive way with the unique and smart guided controls. The LED indicators guide you through the different functions of your coffeemaker to make your coffee experience even more convenient.

Specifications

Performance

Personal coffee memory: no
Strength select: strong or regular
Fresh milk specialities: café latte, cappuccino, latte macchiato, frothed milk
Brewing time 1 cup: 45 sec
Brewing time 2 cups: 75 sec
Programmable cup volume: No

Finishing

Material of spout: Chromed synthetic resin

Easy to use

Touch panel
2 cups at the same time
Adjustable drip tray
Automatic shut off time: 15 min
Direct start
Removable drip tray
Empty tank indication
2 cappuccinos at the same time
2 lattes at the same time
2 macchiatos at the same time
Removable water tank

Easy to clean

Easy-clean button
Calc indicator
Dishwasher proof parts
Two packs of descaler included

Design

Spray paint: No
Chromed spout
Copper chromed spout: No
No. of milk connectors: 1
Stainless steel riser pipe: No
Texture
Finishing: Soft touch

Sustainability

Sustainability certification: Green tick
Energy consumption: 0.26 W (on stand-by)
Made of recycled materials: 90% (paperwork and packaging)

Service

2-year worldwide guarantee

Technical specifications

Power: 2650 W
Frequency: 50 Hz
Voltage: 230 V
Cord length: 80 cm
Country of origin: Made in Poland, Designed in the Netherlands
Supported coffee types: SENSEO® coffee pods
Water pressure in pump: 1 bar (filter coffee & crema)

Weight and dimensions

Product weight: 2.4 kg
Maximum cup height: 85 - 135 mm
Product dimensions (L x D x H): 217 x 280 x 290 mm
Water tank capacity: 1 L

