



**SENSEO® Latte Duo Plus**  
Coffee pod machine

- Two cappuccinos in one go
- Titanium Black
- Integrated milk frother
- Easy-clean function



**HD7857/50**

Finally two cappuccinos in one go from fresh milk!

SENSEO® variety: six recipes and memory function

Unlimited choice with SENSEO® Latte Duo coffee machine: cappuccino, latte macchiato, latte, strong or mild coffee. You can also prepare frothed milk for kids or create your own recipe. And this is as fast as can be with 2 cups in one go.

**Coffee specialities made with fresh frothed milk**

- Only SENSEO® Latte Duo serves 2 milk drinks at a time
- Enjoy 4 coffee and milk recipes at one touch of a button
- Firm hot milk froth thanks to patented frothing system

**Coffee variety for every moment**

- Select your coffee strength: strong short or mild long
- Delicious coffee crema layer as proof of SENSEO® quality
- Personal coffee memory to remember the coffee you love

**Easy to clean and fast operation**

- Easy clean milk frothing system and descaling program
- Milk frother will draw milk directly from a carton or jug
- Intuitive controls for smart guided operation



\* Based on retail sales volumes

*Senseo*

**PHILIPS**

# Highlights

## 2 milk drinks at a time



Save time and effort with the patented Duo Latte function in your SENSEO® Latte Duo coffee maker. Make 2 cups of any coffee specialty you like at the same time at the touch of only one button. Enjoy making your coffee specialty preparation as easy and effortless as never before.

## Fresh milk coffee specialties



Enjoy your delicious SENSEO® cappuccino, latte macchiato or café latte with a rich combination of coffee and fresh milk. Each cup is crowned with a creamy foam layer, just like the ones you can enjoy in coffee bars!

## Strength select function




Prepare your favourite cup of coffee by adjusting the strength and intensity of its taste. With the strength select function on your SENSEO®, you can choose between strong short and mild long coffee.

## Smart guided controls



Operate your Philips coffee maker in a modern and intuitive way with the unique and smart-guided controls. The LED indicators guide you through the different functions of your coffee maker to make your coffee experience even more convenient.

## Easy clean system



All parts in your Philips SENSEO® Latte Duo coffee maker that come into contact with milk

can be cleaned thoroughly through the One-Touch cleaning routine after each use. Or simply disassemble the milk spout and wash all parts thoroughly by hand or in the dishwasher at the end of the day. The machine also will remind you when to descale your appliance.

## Hot, creamy milk froth



SENSEO®'s patented frothing system uses state-of-the-art technology for excellent performance, delivering a perfect, hot milk speciality every time.

## Delicious coffee crema layer



The fine SENSEO® coffee selection and the unique SENSEO® brewing system make sure that your perfect cup of coffee always comes with a rich and delicious coffee foam layer - proof of premium taste and quality.

# Specifications

## Country of origin

- Made in: Poland

## General specifications

- Special functions: Automatic milk frother
- Coffee drinks: Café Crème, Café Latte, Cappuccino, frothed milk, Latte Macchiato
- Suitable for: SENSEO® Coffee pods
- Cups at the same time: 2
- Coffee strength settings: 2
- Customise each drink: Memo function cup volume, Adjustable coffee strength
- Ease of use and comfort: Adjustable spout, Direct start, Removable drip tray, Removable water tank, Automatic shut-off
- Ease of cleaning and maintenance: Automatic descaling cycle, Easy-clean function, Descale indicator, Dishwasher-safe parts

## Finishing

- Material boiler: Metal and glass-filled polyamide
- Material water tank: Plastic
- Material of spout: Copper chromed plastic
- Material drip tray: Plastic
- Material of main body: Plastic

## Design

- Colour: Titanium Black

## Sustainability

- Power consumption stand-by: 0.26 W
- Power consumption brewing: 2650 W
- Made of recycled materials: 90% (paperwork and packaging)

## Service

- 2 year guarantee

## Technical specifications

- Pump pressure: 1 bar
- Brewing time two cups: 75 sec
- Brewing time one cup: 45 sec
- Capacity water tank: 1 l
- Max. cup height: 85 - 135 mm
- Cord length: 0.8 m
- Frequency: 50 Hz
- Voltage: 230 V
- Water boilers: 1
- Capacity water tank: Up to 7 cups

## Weight and dimensions

- Dimensions of product (W x D x H): 218 x 280 x 290 mm
- Weight of product: 2.4 kg