



**SENSEO® Quadrante**  
Coffee pod machine

- Adjustable tray height
- Chinese red and platinum
- Strength select function



HD7864/81

## Delicious coffee at a touch, in a modern design

Enjoy SENSEO® quality and choose the strength of your coffee

Add some style to your home with the SENSEO® Quadrante coffee machine. Enjoy your coffee with the trusted SENSEO® brewing system, now with adjustable tray so you can use your favourite cup.

### Always a delicious cup of coffee

- Delicious coffee crema layer as proof of SENSEO® quality
- The machine is tested more than 10,000 times to ensure consistent quality
- Unique brewing system for optimal taste and temperature

### Coffee variety for every moment

- Choose between 2 recipes: strong short or mild long coffee
- Variety of coffee blends and flavours for different tastes

### Fast and easy operation

- Unique coffee machine that brews 2 cups at a time
- Adjustable drip tray to fit your favourite cup
- 30 minutes auto shut-off for energy saving and safety
- Coffee at the touch of a button



\* Based on retail sales volumes

*Senseo*

**PHILIPS**

# Highlights

## Delicious coffee crema layer



The fine SENSEO® coffee selection and the unique SENSEO® brewing system make sure that your perfect cup of coffee always comes with a rich and delicious coffee foam layer - proof of premium taste and quality.

## One-button operation



With this coffee pod machine you can easily prepare one or two cups of coffee with the simple one-button operation.

## Adjustable drip tray



By raising or lowering the drip tray you can adjust your Philips SENSEO® coffee maker to the size of your favourite cup or mug.

## Variety of blends and flavours



SENSEO® offers you a large variety of coffee blends and flavours, each with its own distinctive taste to fit your personal preference.

## 1 or 2 cups at the same time



This SENSEO® coffee maker prepares one or two cups of your delicious SENSEO® coffee in less than a minute.

## Strength select function



Prepare your favourite cup of coffee by adjusting the strength and intensity of its taste. With the strength select function on your SENSEO®, you can choose between strong short and mild long coffee.

# Specifications

## General specifications

- Cups at the same time: 2
- Compatible coffee serving: SENSEO® Coffee pods
- Customise each drink: Adjustable coffee strength
- Ease of use and comfort: Adjustable spout, Removable drip tray, Automatic shut-off
- Ease of cleaning and maintenance: Dishwasher-safe parts
- Coffee drinks: Café Crème

## Finishing

- Material boiler: Metal and glass-filled polyamide
- Material drip tray: Metal
- Material of main body: Plastic
- Material of spout: Chromed synthetic resin
- Material water tank: Plastic

## Country of origin

- Made in: Poland

## Weight and dimensions

- Weight of product: 2.79 kg
- Dimensions of product (W x D x H): 190 x 270 x 290 mm
- Dimensions of packaging (W x D x H): 224 x 320 x 328 mm

## Design

- Colour: Chinese Fire

## Sustainability

- Energy consumption: 0.35 W (on stand-by), 1450 W (while brewing)
- Power consumption stand-by: 0.35 W
- Power consumption brewing: 1450 W
- Made of recycled materials: 90% (paperwork and packaging)

## Service

- 2 year guarantee

## Technical specifications

- Pump pressure: 1 bar
- Max. cup height: 75 - 125 mm
- Brewing time one cup: 30 sec
- Water boilers: 1
- Brewing time two cups: < 60 sec
- Cord length: 0.8 m
- Capacity water tank: 1.2 l
- Country of origin: Made in Poland, Designed in the Netherlands
- Frequency: 60 Hz
- Voltage: 220 - 240 V