

SENSEO® Switch
Pod and filter coffee
machine

- Pad and filter machine
- DualBrew technology
- 2 cups included
- Cashmere grey

HD7892/29



A jug to share or a cup just for you

The only 2-in-1 coffee maker with filter and pads

Brew your favorite big pot of filter coffee to share, or with the push of a button, enjoy the various Senseo blends just for you. With our simple and easy to use DualBrew technology, you can now brew jugs, cups, filter and pad coffee.

Coffee variety for every moment

- DualBrew technology for filter and pad coffee in one machine
- Variety of pad and filter coffee blends for every moment
- Stainless steel thermal jug for 7 cups of filter coffee
- 1 or 2 cups Senseo® coffee in less than a minute

Enjoy the best tasting Senseo® and filter coffee

- Stainless steel thermal jug for a hot cup of filter coffee
- Delicious crema layer as proof of Senseo® quality
- Machine is tested >10.000 times to ensure consistent quality

Fast and easy operation

- Brew jugs and cups at the touch of a button
- 1L water tank to brew up to 7 cups in one go
- The decalcifying light reminds you when to descale
- Direct auto shut-off after brewing for energy saving



* Based on retail sales volumes

Senseo®

PHILIPS

Pod and filter coffee machine
Pad and filter machine DualBrew technology, 2 cups included, Cashmere grey

HD7892/29

Highlights

DualBrew Technology



Drink your coffee at its best. DualBrew Technology ensures that each cup of Senseo® coffee and each jug of filter coffee is brewed into perfection with the right pressure and amount of water.

Variety of pad & filter coffee



With Senseo® Switch you can enjoy a large variety of pad and filter coffee blends and flavors. Therefore you can always drink the coffee you like the most.

Jug for 7 cups



The stainless steel thermal jug offers you to brew up to 7 cups of authentic filter coffee in

one go. Ideal for a lazy Sunday morning breakfast or when you want to enjoy coffee together.

1 or 2 cups at the same time



This Senseo® coffeemaker prepares one or two cups of delicious Senseo® coffee from pads in less than a minute.

Stainless steel thermal jug



The stainless steel thermal jug maintains the temperature and aroma for hours

Delicious crema layer



The fine Senseo® pad selection and the DualBrew technology make sure that your

perfect cup of Senseo® pad coffee always comes with a rich and delicious crema layer.

Machine is tested >10.000 time



Philips tests their coffee makers during the development process for more than 10.000 cups of coffee. This ensures high quality and durability

One touch operation



With its simple 3 button interface you can brew 1 cup, 2 cups and a jug at the touch of a button.

1L water tank



Thanks to the 1 liter water tank you can brew up to 7 cups of coffee without refilling.

Specifications

Accessories

- Included: Cups, Pod holder, Unbreakable thermal jug

Design

- Color: Cashmere grey

Country of origin

- Made in: Romania

General specifications

- Cups at the same time: 2 to 7
- Ease of cleaning & maintenance: Descaler indicator, Removable filter holder
- Ease of use and comfort: Removable drip-tray, Removable water tank, Water level indication

Sustainability

- Packaging: > 90% recycled materials
- Power consumption brewing: 1450 W
- User manual: 100% recycled paper

Service

- 2-year guarantee

Technical specifications

- Brewing time one cup: 30 sec
- Capacity water tank: 1 L
- Capacity water tank: 7 cups
- Cord length: 0.8 m
- Frequency: 50 Hz
- Max. cup height: 130 mm
- Pump pressure: 1 bar
- Brewing time for a jug: 8.5 min

Weight and dimensions

- Dimensions of packaging (WxDxH): 466 x 242 x 322 mm
- Dimensions of product (WxDxH): 150 x 400 x 270 mm
- Weight incl. packaging: 2.4 kg
- Weight of product: 1.75 kg