

# PHILIPS

## Saeco

### Manual Espresso

### Focus



HD8323/01



## Authentic Italian Espresso every day

With pressurized filter Crema

Philips-Saeco manual espresso machine offers enthusiasts of traditional preparation everything for a perfect daily espresso. The patented pressurized filter Crema guarantees a long lasting delicious crema, at every use.

#### Authentic Italian Espresso

- Pressurized filter Crema
- 15 bar pump
- Cup holder

#### Simplicity and speed of use

- Grind coffee and Easy Serving Espresso (E.S.E.)
- Pannarello to froth milk as you like
- Ergonomic in day by day operations

#### Every day use

- Long lasting premium materials

# Highlights

## Pressurized filter Crema



This special crema filter guarantees a long lasting delicious crema

## Grind coffee and Easy Serving



For your convenience you can choose between ground coffee and Easy Serving Espresso (E.S.E.) pads.

## Pannarello



With the pannarello you can froth your milk exactly according to your preferences. Just dip the pannarello in the milk, while slowly stirring

the milk with a rotary movement. Froth the milk as long as you want for more or less foamy mikfroth.

## 15 bar pump



High pressure ensures that the coffee beans entire aroma is always fully extracted

## Long lasting premium materials



Philips Saeco Manual Espresso features high quality and durable housing material

## Ergonomic in day by day



Refilling coffee powder or water, emptying the filter or the drip tray. All compartments are directly accessible for maximum convenience.

## Cup holder



With this practical feature you can store your cups and glasses right on the machine - always within reach and conveniently stored without taking up space.

# Specifications

## Features

Brita Filter compatible: Optionable  
Cupholder  
Cupwarmer: No  
Filterholder: Pressurized "Crema"  
Hot water / Steam Nozzle  
Interface: Rotary Switch  
Kit Pods E.S.E  
Pannarello: Plastic  
Simultaneous brewing

## Design

Colour: Black and Chrome  
Materials and finishing: ABS

## Technical specifications

Boiler material: Inox

## Technical data

Power: 1050 W  
Pump Pressure: 15 bar

## Logistic data

Pallet number of pieces: 40  
Pallet size: 80,0 x 120,0 x 205,0 cm

## Weight and dimensions

Product dimensions (L x D x H):  
200x265x297 mm  
Weight: 4 kg

## Water tank

Water tank capacity: 1 l

