



Saeco Xsmall Super-automatic espresso machine

- Brews 2 coffee varieties
- Classic Milk Frother
- Beige
- 5 step adjustable grinder

HD8645/57



Taste the aroma of your favourite coffee beans

One touch super-automatic espresso machine

Whatever blend of coffee you wish to try next, the Xsmall will grind the beans fresh on the spot at the touch of a button. It comes also equipped with a manual frother to add a touch of velvety pleasure to all your fresh coffee drinks.

Advanced technology designed for coffee perfection

- Delicious milk froth thanks to the classic milk frother
- 20,000 cups of finest coffee with durable ceramic grinders
- Fine-tune the coffee's richness with 5 grinder settings
- Enjoy hot coffee in no time with the Quick Heat Boiler

Set the beverages to suit your taste

- Save your favorite coffee length


Ease of cleaning and maintaining

- Always a clean machine thanks to automatic circuit cleaning
- Easy cleaning thanks to dishwasher-safe drip tray
- The fully removable brewing group can be cleaned in no time

PHILIPS

Saeco, a Philips brand

 **Saeco**



Highlights

Classic milk frother



This Saeco espresso machine comes with the classic milk frother that baristas call a "Pannarello". It dispenses steam and is immersed in milk to prepare gorgeous milk foam. Unleash your inner barista by preparing your delicious milk specialties the traditional way!

100% Ceramic grinders



Our grinders are made of high-tech ceramic: exceptionally hard and precise. Fresh beans are gently ground, without risk of overheating: extracting all the best flavors and aroma, delivering a superior coffee taste for at least 20,000 cups.

5-steps adjustable grinders



When it comes to the fineness of the grind, this machine never fails to satisfy. Different coffee blends require different levels of granularity for the full flavor to unfold. So the grind granularity of this machine has five adjustable settings - from the finest grind for a full-bodied espresso, to the coarsest for a lighter coffee.

Automatic circuit cleaning



Saeco designed this espresso machine to automatically clean its coffee circuit with water upon starting up or switching off of the machine, this delivers a great, fresh taste with each cup of coffee.

Saves your coffee length



You will always get a perfect cup of espresso brewed according to your personal preference thanks to our memo function which allows you to adjust the coffee length to suit your taste. Enjoy a superb coffee drink with just the press of a button.

Dishwasher-safe drip tray



For your convenience, you can wash the drip tray of your Saeco in the dishwasher. This will save time and ensure a hygienic cleaning.

Specifications

Weight and dimensions

- Dimensions of product (WxDxH): 420 x 325 x 295 mm
- Weight of product: 6.9 kg

Service

- 1-year guarantee

Technical specifications

- Frequency: 50 Hz
- Voltage: 230 V
- Capacity bean container: 180 gr
- Capacity waste container: 8 servings
- Capacity water tank: 1 L
- Cord length: 0,8 m
- Pump pressure: 15 bar
- Water boilers: 1
- Max. cup height: 95 mm

Country of origin

- Made in: Romania

General specifications

- Ease of cleaning & maintenance: Automatic rinse cycle, Removable brewing group
- Ease of use and comfort: Removable water tank
- Special functions: Pre-brewing, Manual milk frother Pannarello
- Suitable for: Whole coffee beans

Accessories

- Included: Descaler pack, Water filter

Design

- Color: Beige

Finishing

- Material panarello: Plastic
- Material boiler: Stainless steel (Inox)
- Material of main body: ABS Plastic

Sustainability

- Power consumption brewing: 1400 W