

PHILIPS

Fully automatic
espresso machines

2100 Series

4 Beverages

Easy Cappuccino System

Silver



HD8652



Great Cappuccino, small machine

OneTouch cappuccino from fresh milk now convenient

There's nothing complicated about delicious espresso and creamy cappuccino. With the new 2100 series, your favorite drink is just one touch away, all delivered by a small and hassle free machine which fits your kitchen as well as your life.

A variety of coffees customized to your taste

- Enjoy 4 coffees at your fingertips
- Preparing your cappuccino has never been easier
- Adjust and store your personal user profile
- Adjust the length, 2 aroma strength and 5 grinder settings

Your fresh coffee experience

- 20,000 cups of finest coffee with durable ceramic grinders
- Coffee at the perfect temperature with our Thermoblock
- Always the right strength in cup, no matters which beans

Enjoy your coffees every day with no hassle

- Clean milk residues after every use with milk clean function
- External milk container included, easy to clean and store
- Fits any kitchen thanks to the small size and frontal access
- Enjoy a great coffee with Auto-Rinse & guided descaling
- Easy cleaning thanks to fully removable brew group

Highlights

Easy Cappuccino System



You can get a perfectly brewed espresso right in your cup from freshly ground beans, simply push a button and wait a few seconds. Now, with the new Easy Cappuccino System, your one touch cappuccino has never been so easy.

External milk container



Enjoy your creamy cappuccino with the milk you prefer thanks to the external milk container, dishwasher safe. Easily unplug it from the machine and put it in the fridge for long lasting freshness. Cappuccino with every kind of milk has never been so easy.

Customize your coffees



This Super-Automatic machine offers an abundance of indulgent options to customize your beverage to your taste. You can easily personalize and memorize length and strength for each drink. Feel free to explore, experiment and dream up any drink!

100% ceramic grinders



Our grinders are 100% pure ceramic: extremely hard and precise, so you can enjoy fresh aromatic coffee, for at least 20.000 cups.

4 aromatic coffees



Enjoy your favourite coffees for your special moments. Whether you crave for an espresso, a coffee or a milk based recipe, your fully-automatic machine delivers a perfect in-cup result with no hassle and in no time!

Gusto perfetto



Gusto Perfetto is self learning technology that tracks constantly the beans you use to prepare your drinks. If it detects a change in the type of beans used, it automatically adjust the dosing in the brew chamber to always ensure a consistent result in cup

Thermoblock



The Thermoblock ensures a hot coffee and cappuccino for your family always at the perfect temperature. The secret is in its light aluminum and stainless steel body, which can reach hot temperatures, fast.

Quick Milk clean



The unique one-touch carafe quick clean allows you to thoroughly rinse the milk system at your convenience after every use

Removable brew group



The brew group is the heart of every fully automatic coffee machine, and should be cleaned regularly. The removable brew group allows you to clean it thoroughly just by rinsing it under the tap.

Specifications

Customization

Aroma Strength Settings: 2
Coffee Length: Adjustable
Grinder Settings: 5
Pre Brew Aroma control: No
User Profiles: 1

General specifications

Milk Solution: Easy Cappuccino
User Interface: LED Buttons

Other features

Auto-Rinse & Guided descaling
Main Switch ON / OFF button
Quick Heat Boiler
Removable brew group
Gusto perfetto

Technical specifications

Capacity milk carafe: 0.5 L
Capacity waste container: 8 servings
Capacity water tank: 1 L
Frequency: 60 Hz
Max. cup height: 95 mm
Voltage: 120 V
Color & Finishing: Silver Paint

Filter compatibility: Brita Intenza

Waste container: Frontal access

Water tank: Frontal access

Weight of product: 7 kg

Product dimensions: 295 x 325 x 420 mm

Coffee bean capacity: 180 g

Cord length: <100 cm

Variety

Beverages: Espresso, Espresso Lungo, Hot water, Cappuccino

Coffee Powder Option: No

Double Cup

Milk Double Cup: No

