



**Saeco Minuto  
Super-automatic  
espresso machine**

- Brews 2 coffee varieties
- Classic Milk Frother
- Black
- 5 step adjustable grinder



HD8661/01

Always your favorite beverage at just one touch  
with the one-click removable brewing group

Only Saeco Minuto delivers the real first bean to cup experience with maximum convenience, top-notch performances and large capacities in extra compact dimensions

**Advanced technology designed for coffee perfection**

- Fine-tune the coffee's richness with 5 grinder settings
- 20,000 cups of finest coffee with durable ceramic grinders
- Velvety milk foam with the Classic Milk Frother

**High comfort is part of the experience**

- The fully removable brewing group can be cleaned in no time

**PHILIPS**

Saeco, a Philips brand

 **Saeco**



# Highlights

## 5-steps adjustable grinders



When it comes to the fineness of the grind, this machine never fails to satisfy. Different coffee blends require different levels of granularity for the full flavor to unfold. So the grind granularity of this machine has five adjustable settings - from the finest grind for a full-bodied espresso, to the coarsest for a lighter coffee.

## 100% Ceramic grinders



Our grinders are made of high-tech ceramic: exceptionally hard and precise. Fresh beans are gently ground, without risk of overheating: extracting all the best flavors and aroma, delivering a superior coffee taste for at least 20,000 cups.

## Removable brewing group



Efficiency and ease of use were key inspirations when Saeco invented the first brewing group 30 years ago. And to this day, it still proves to be an inspired, resolute piece of technology. As always, it's so simple to clean – just remove it and wash it under the tap for a few seconds, then re-insert it just as easily.

## Classic Milk Frother



The Classic Milk Frother is for those who love to assume the role of master craftsman, and it's just easy. Within seconds you can create a rich, silky layer of foam - the crowning glory of your coffee.

# Specifications

## Country of origin

- Made in: Europe

## Sustainability

- Power consumption brewing: 1850 W

## General specifications

- One touch variety: 3
- Grinder settings: 5
- Customizing per drink: Adjustable coffee strength, Adjustable cup volume
- Coffee drinks: Espresso, Cappuccino, hot water, Café Crème, frothed milk, Espresso Macchiato, Latte Macchiato
- Suitable for: Whole coffee beans
- Cups at the same time: 2
- Ease of use and comfort: Removable spout, Removable drip-tray
- Type of boiler: Quick heat boiler
- Ease of cleaning & maintenance: Automatic rinse cycle, Optional Brita water filter, Automatic descaling cycle, Removable brewing group
- Special functions: Ceramic grinder, Pre-brewing, Manual milk frother Pannarello

## Finishing

- Material boiler: Stainless steel (Inox)
- Material drip tray: Stainless steel
- Material water tank: Plastic
- Material panarello: Stainless steel
- Material of main body: Plastic

## Service

- 2-year guarantee

## Technical specifications

- Brewing time one cup: 45 (espresso) to 100 (long coffee) sec
- Capacity water tank: 1.8 L
- Max. cup height: 152 mm
- Capacity bean container: 250 gr
- Cord length: 0.8 m
- Water boilers: 1
- Capacity waste container: 15 servings
- Frequency: 50 Hz
- Voltage: 230 V
- Pump pressure: 15 bar

## Weight and dimensions

- Dimensions of product (WxDxH): 215 x 429 x 330 mm
- Weight of product: 7.5 kg

## Design

- Color: Black