

PHILIPS

Saeco

Super-automatic
espresso machine

Xsmall

Black



HD8743/03



Taste the aroma of your favorite coffee beans Coffee machine with one touch bean-to-cup espresso

Saeco Xsmall coffee machine, the smallest member of the bean-to-cup family, combines design and functionality. Preparing an excellent espresso is done with one push of a button – your fresh coffee beans are ground for intense aroma.

Grind your favorite coffee beans

- One touch bean-to-cup espresso
- Small and energy efficient
- Adjustable Grinders

Easy to use

- Ergonomic in day-by-day operations

Ease of cleaning and maintaining

- Always a clean machine thanks to automatic circuit cleaning
- Easy cleaning thanks to removable brewing group

Highlights

Bean-to-cup espresso



Your favorite beans are always freshly ground so their entire aroma is captured in every cup. This way Saeco bean-to-cup espresso machines deliver excellent and fresh coffee enjoyment day after day.

Automatic circuit cleaning



Saeco designed this espresso machine to automatically clean its coffee circuit with water upon starting up or switching off of the machine, this delivers a great, fresh taste with each cup of coffee.

Removable brewing group



The brewing group, a Saeco invention, is the heart of our espresso machines, ensuring automation. The brewing group is, depending on the model, easily accessible from the front or side. It can be removed effortlessly for easily cleaning by rinsing under the tap ensuring maximum hygiene.

Small and energy efficient



Small size and frontal access to all functionalities make sure that the Philips Saeco Xsmall automatic espresso machine fits in every kitchen. And thanks to its efficiency (Class A according to Swiss regulation) and auto shutdown it's very kind to the environment.

Ergonomic day-by-day



Saeco is a synonym for convenience: refilling beans or water, emptying the coffee-dump box or the drip tray, all compartments of the full automatic coffee machine are directly accessible.

Adjustable Grinders



Adjustable Grinders

Specifications

Technical specifications

Number of water boilers: 1 boiler

Supported coffee types: Whole coffee beans

Perfect Espresso

Espresso technology: Aroma-system: pre-brewing

Service

2-year worldwide guarantee

Easy to use

Cleaning and maintenance: Automatic coffee circuit rinse

Usage: Removable brewing group, Removable watertank

Technical data

Boiler: Stainless steel

Frequency: 50 Hz

Power: 1400 W

Voltage: 240 V

Pump Pressure: 15 bar

Weight and dimensions

Maximum cup height: 95 mm

Product dimensions (L x D x H):

420x325x295 mm

Coffee bean capacity: 180 gr

Waste container capacity: 8 servings

Water tank capacity: 1 L



Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO₂ emissions.

How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.