

PHILIPS

Saeco

Super-automatic
espresso machine

Xsmall

Brews 2 coffee varieties

Class

Vanilla

5-step adjustable grinder

HD8745/12



Taste the aroma of your favourite fresh beans

One touch bean-to-cup espresso

Xsmall the smallest member of the bean-to-cup family combines design and functionality. Preparing an excellent espresso is done with one push of a button - your favourite beans are freshly ground for intense aroma.

Grind your favourite coffee beans

- One touch bean-to-cup espresso
- Small and energy efficient
- Adjustable Grinders

Easy to use

- Delicious milk froth thanks to the classic milk frother
- Ergonomic in day to day operation

Easy to clean and maintain

- Always a clean machine thanks to automatic circuit cleaning
- Easy cleaning thanks to removable brewing group

Highlights

Bean-to-cup espresso



Your favourite beans are always freshly ground so their entire aroma is captured in every cup. This way, Saeco bean-to-cup espresso machines deliver excellent and fresh coffee enjoyment day after day.

Automatic circuit cleaning



Saeco designed this espresso machine to automatically clean its coffee circuit with water when the machine is started up or switched off. This delivers a great, fresh taste with each cup of coffee.

Classic milk frother



This Saeco espresso machine comes with the classic milk frother that baristas call a "Pannarello". It dispenses steam and is

immersed in milk to prepare gorgeous milk foam. Unleash your inner barista by preparing your delicious milk specialties the traditional way!

Removable brewing group



The brewing group, a Saeco invention, is the heart of our espresso machines, ensuring automation. The brewing group is, depending on the model, easily accessible from the front or side. It can be removed effortlessly for easy cleaning by rinsing under the tap, ensuring maximum hygiene.

Small and energy efficient



Small size and front access to all functionalities ensure that the Philips Saeco Xsmall automatic espresso machine fits in every kitchen. And thanks to its efficiency (Class A according to Swiss regulation) and auto-shutdown it's very kind to the environment.

Ergonomic day to day



Saeco is a synonym for convenience: refilling beans or water, emptying the coffee-dump box or the drip tray, all compartments of the full automatic coffee machine are directly accessible.

Adjustable Grinders



Adjustable Grinders

Specifications

Technical specifications

Boiler material: Stainless steel (Inox)

Country of origin: Designed in Italy, Made in Europe

Power: 1400 W

Voltage: 230 V

Frequency: 50 Hz

Cord length: 80 cm

Perfect Espresso

Espresso technology: Aroma-system: pre-brewing

Easy to use

Cleaning and maintenance: Automatic coffee circuit rinse

Usage: Removable brewing group, Removable water tank

Weight and dimensions

Product weight: 6.9 kg

Product dimensions (L x D x H): 420 x 325 x 295 mm

Coffee bean capacity: 180 gr

Waste container capacity: 8 servings

Water tank capacity: 1 l

