

# PHILIPS

## Saeco

Automatic espresso  
machine

Xsmall

Class

Black



HD8745/21



## Taste the aroma of your favorite fresh beans

### One touch bean-to-cup espresso

Xsmall the smallest member of the bean-to-cup family combines design and functionality. Preparing an excellent espresso is done with one push of a button - your favorite beans are freshly ground for intense aroma.

#### **Grind your favorite coffee beans**

- One touch bean-to-cup espresso
- Adjustable ceramic grinders
- Small and energy efficient

#### **Easy to use**

- Pannarello to froth milk as you like
- Ergonomic in day-by-day operations

#### **Easy to clean and maintain**

- Automatic coffee circuit cleaning
- Removable brewing group

# Highlights

## Bean-to-cup espresso



Your favorite beans are always freshly ground so their entire aroma is captured in every cup. This way Philips-Saeco bean Saeco bean-to-cup espresso machines deliver excellent and fresh coffee enjoyment day after day.

## Adjustable ceramic grinders



Whole beans are freshly ground for every cup by ceramic grinders, always preserving their full aroma and never overheating the coffee.

## Auto coffee circuit cleaning



This feature makes sure that each and every coffee is as fresh as possible: Before going into and when returning from stand-by mode, the machine automatically cleans its coffee circuit.

## Pannarello



With the pannarello you can froth your milk exactly according to your preferences. Just dip the pannarello in the milk, while slowly stirring the milk with a rotary movement. Froth the milk as long as you want for more or less foamy mikfroth.

## Removable brewing group



The brewing group is at the heart of every fully automatic coffee machine and it should always be kept clean. A task that doesn't get any more convenient than with a Saeco: remove, rinse and re-insert – finished.

## Small and energy efficient



Small size and frontal access to all functionalities make sure that the Xsmall fits in every kitchen. And thanks to its efficiency (Class A according to Swiss regulation) and auto shutdown it's very kind to the environment.

## Ergonomic day-by-day



Philips-Saeco is a synonym for convenience: refilling beans or water, emptying the coffee-dump box or the drip tray, all compartments are directly accessible.

# Specifications

## Perfect Espresso

**Espresso technology:** Aroma-system: pre-brewing

## Easy to use

**Cleaning and maintenance:** Automatic coffee circuit rinse

**Usage:** Removable brewing group, Removable watertank

## Technical data

**Boiler:** Stainless steel

**Frequency:** 50 Hz

**Power:** 1400 W

**Voltage:** 230 V

**Pump Pressure:** 15 bar

## Weight and dimensions

**Dimensions:** 295x325x420 mm

**Coffee bean capacity:** 180 gr

**Dump box capacity:** 8 servings

**Water tank capacity:** 1 l

