

PHILIPS

Saeco

Super-automatic
espresso machine

Xsmall

Brews 2 coffee varieties

Classic Milk Frother

Silver

5 step adjustable grinder

HD8745/47



Taste the aroma of your favorite coffee beans one touch bean to cup espresso

Whatever coffee you wish to try next, the Saeco Xsmall will grind the beans fresh on the spot at the touch of a button. It comes equipped with a steam pipe to add a touch of milk froth pleasure to all your fresh coffee drinks.

Advanced technology designed for coffee perfection

- Fine-tune the coffee's richness with 5 grinder settings
- Extract maximum flavor with the 100% ceramic grinders
- Velvety milk foam with the Classic Milk Frother

High comfort is part of the experience

- The fully removable brewing group can be cleaned in no time
- Auto-cleaning cycle removes any hassle

Highlights

5-steps adjustable grinders




When it comes to the fineness of the grind, this machine never fails to satisfy. Different coffee blends require different levels of granularity for the full flavor to unfold. So the grind granularity of this machine has five adjustable settings – from the finest grind for a full-bodied espresso, to the coarsest for a lighter coffee.

100% Ceramic grinders



The robust 100% ceramic grinders guarantee a moment of pure coffee indulgence for years to come. The ceramic material creates the ideal grind, which allows the water to flow through steadily, extracting the purest essence of the beans. And unlike other 'regular' grinders, the ceramic material prevents the coffee from overheating and tasting burnt.

Removable brewing group



Efficiency and ease of use were key inspirations when Saeco invented the first brewing group 30 years ago. And to this day, it still proves to be an inspired, resolute piece of technology. As always, it's so simple to clean – just remove it and wash it under the tap for a few seconds, then re-insert it just as easily.

Auto-cleaning



The automatic cleaning cycle makes it easy to look after, and it increases the machine's longevity – giving you more time to enjoy your coffee instead of cleaning up.

Classic Milk Frother



The Classic Milk Frother is for those who love to assume the role of master craftsman, and it's just easy. Within seconds you can create a rich, silky layer of foam – the crowning glory of your coffee.

Specifications

Finishing

Material drip tray: Stainless steel

Material panarello: Plastic

Material water tank: Plastic

Material boiler: Stainless steel (Inox)

Material of main body: Plastic

Service

1-year guarantee

Country of origin

Made in: Europe

General specifications

Coffee drinks: Espresso, Cappuccino, hot water, Café Crème, frothed milk, Espresso Macchiato, Latte Macchiato

Suitable for: Whole coffee beans, ground coffee powder

Cups at the same time: 2

Ease of cleaning & maintenance: Removable brewing group, Automatic rinse cycle, Dishwasher-safe parts, Automatic de-scaling cycle

Ease of use and comfort: Removable water tank, Removable drip-tray

Special functions: Manual milk frother Pannarello, Ceramic grinder, Pre-brewing, Hot water option, Steam option

Type of boiler: Stainless steel boiler

Sustainability

Power consumption brewing: 1400 W

Technical specifications

Pump pressure: 15 bar

Capacity bean container: 180 gr

Capacity waste container: 8 servings

Capacity water tank: 1 L

Cord length: 0.8 m

Frequency: 60 Hz

Max. cup height: 95 mm

Voltage: 120 V

Water boilers: 1

Pump pressure: 15 bar

Weight and dimensions

Dimensions of product (WxDxH): 295 x 420 x 325 mm

Weight of product: 8.0 kg

Design

Color: Black, Silver

