

PHILIPS

Saeco

Super-automatic
espresso machine

Xsmall

Brews 2 coffee varieties

Classic Milk Frother

Silver

5 step adjustable grinder



HD8745/57



Philips Saeco Xsmall

one touch bean to cup espresso

Whatever coffee you wish to try next, the Saeco Xsmall will grind the beans fresh on the spot at the touch of a button. It comes equipped with a manual frother to add a touch of milk froth pleasure to all your fresh coffee drinks.

Authentic Italian coffee perfection

- Delicious milk froth thanks to the classic milk frother
- Coffee without burnt taste thanks to 100% ceramic grinders

Set the beverages to suit your taste

- Save your favorite coffee length
- Play with the coffee's richness with our adjustable grinders

Ease of cleaning and maintaining

- Always a clean machine thanks to automatic circuit cleaning
- Easy cleaning thanks to removable brewing group

Highlights

Automatic circuit cleaning




Saeco designed this espresso machine to automatically clean its coffee circuit with water upon starting up or switching off of the machine, this delivers a great, fresh taste with each cup of coffee.

100% ceramic grinders



This espresso machine is equipped 100% ceramic grinders. Saeco uses ceramic grinders because of their consistent grind without overheating the coffee bean for an impeccable espresso. Ceramic also ensures long-lasting performance and a totally silent operation.

Saves your coffee length



You will always get a perfect cup of espresso brewed according to your personal preference thanks to our memo function which allows you to adjust the coffee length to suit your taste. Enjoy a superb coffee drink with just the press of a button.

Classic milk frother




This Saeco espresso machine comes with the classic milk frother that baristas call a "Pannarello". It dispenses steam and is immersed in milk to prepare gorgeous milk foam. Unleash your inner barista by preparing your delicious milk specialties the traditional way!

5 step adjustable grinders



Different coffee blends require different levels of granularity for the full flavor to unfold. The grind granularity of this espresso machine can be adjusted in 5 settings, from the finest grind, for a full bodied espresso, to the coarsest, for a lighter coffee.

Removable brewing group



The brewing group, a Saeco invention, is the heart of our espresso machines, ensuring automation. The brewing group is, depending on the model, easily accessible from the front or side. It can be removed effortlessly for easily cleaning by rinsing under the tap ensuring maximum hygiene.

Specifications

Perfect Espresso

Espresso technology: Aroma-system: pre-brewing

Finishing

Material panarello: Plastic

Easy to use

Cleaning and maintenance: Automatic coffee circuit rinse

Usage: Removable brewing group, Removable watertank

Weight and dimensions

Product dimensions (L x D x H): 420 x 325 x 295 mm

Coffee bean capacity: 180 gr

Waste container capacity: 8 servings

Water tank capacity: 1 L

Maximum cup height: 95 mm

Product weight: 7.2 kg

Design

Materials and finishing: ABS Plastic

Service

1-year consumer warranty

Technical specifications

Cord length: 80 cm

Boiler material: Stainless steel (Inox)

Frequency: 50 Hz

Power: 1400 W

Voltage: 230 V

Number of water boilers: 1 boiler

Country of origin: Designed in Italy, Made in Europe

Removable brewing group

Supported coffee types: Whole coffee beans

Water pressure in pump: 15 bar (perfect espresso)

