

PHILIPS

Saeco

Super-automatic
espresso machine

Xsmall

Brews 2 coffee varieties

Chrome

5 step adjustable grinder



HD8747/03



Taste the aroma of your favorite coffee beans One touch bean-to-cup espresso

Whatever coffee you wish to try next, the Saeco Xsmall will grind the beans fresh on the spot at the touch of a button. It comes equipped with a manual frother to add a touch of milk froth pleasure to all your fresh coffee drinks.

Grind your favorite coffee beans

- One touch bean-to-cup espresso
- Small and energy efficient
- Adjustable Grinders

Easy to use

- Delicious milk froth thanks to the classic milk frother
- Ergonomic in day-by-day operations

Ease of cleaning and maintaining

- Always a clean machine thanks to automatic circuit cleaning
- Easy cleaning thanks to removable brewing group

Highlights

Bean-to-cup espresso



Your favorite beans are always freshly ground so their entire aroma is captured in every cup. This way Saeco bean-to-cup espresso machines deliver excellent and fresh coffee enjoyment day after day.

Automatic circuit cleaning



Saeco designed this espresso machine to automatically clean its coffee circuit with water upon starting up or switching off of the machine, this delivers a great, fresh taste with each cup of coffee.

Classic milk frother



This Saeco espresso machine comes with the classic milk frother that baristas call a "Pannarello". It dispenses steam and is

immersed in milk to prepare gorgeous milk foam. Unleash your inner barista by preparing your delicious milk specialties the traditional way!

Removable brewing group



The brewing group, a Saeco invention, is the heart of our espresso machines, ensuring automation. The brewing group is, depending on the model, easily accessible from the front or side. It can be removed effortlessly for easily cleaning by rinsing under the tap ensuring maximum hygiene.

Small and energy efficient



Small size and frontal access to all functionalities make sure that the Philips Saeco Xsmall automatic espresso machine fits in every kitchen. And thanks to its efficiency (Class A according to Swiss regulation) and auto shutdown it's very kind to the environment.

Ergonomic day-by-day



Saeco is a synonym for convenience: refilling beans or water, emptying the coffee-dump box or the drip tray, all compartments of the full automatic coffee machine are directly accessible.

Adjustable Grinders



Adjustable Grinders

Specifications

Technical specifications

Boiler material: Stainless steel (Inox)

Power: 1400 W

Voltage: 230 V

Frequency: 50 Hz

Cord length: 80 cm

Perfect Espresso

Espresso technology: Aroma-system: pre-brewing

Easy to use

Cleaning and maintenance: Automatic coffee circuit rinse

Usage: Removable brewing group, Removable watertank

Weight and dimensions

Product dimensions (L x D x H): 420x325x295 mm

Coffee bean capacity: 180 gr

Waste container capacity: 8 servings

Water tank capacity: 1 L

