



### Saeco Intuita Super-automatic espresso machine

- Brews 3 coffee varieties
- Automatic Milk Frother
- Silver
- 5 step adjustable grinder

HD8750/81



## Espresso and cappuccino from fresh beans

Select your aroma with this espresso machine

Saeco Intuita espresso machine offers you the possibility to taste freshly ground espresso at the touch of a button, aroma selection, easy to use, easy to customize and easy to clean

#### **Authentic Italian coffee perfection**

- Delicious milk froth thanks to the automatic milk frother
- Coffee without waiting thanks to the quick heat boiler
- Coffee without burnt taste thanks to 100% ceramic grinders

#### **Set the beverages to suit your taste**

- Save your favorite coffee length and strength
- Play with the coffee's richness with our adjustable grinders
- Avoid heat loss and fit every cup with our adjustable spout

#### **Ease of cleaning and maintaining**

- Always a clean machine thanks to automatic circuit cleaning
- Easy cleaning thanks to removable brewing group
- Easy cleaning thanks to dishwasher-safe parts

**PHILIPS**

Saeco, a Philips brand

 **Saeco**



# Highlights

## Automatic circuit cleaning



Saeco designed this espresso machine to automatically clean its coffee circuit with water upon starting up or switching off of the machine, this delivers a great, fresh taste with each cup of coffee.

## 100% ceramic grinders



This espresso machine is equipped 100% ceramic grinders. Saeco uses ceramic grinders because of their consistent grind without overheating the coffee bean for an impeccable espresso. Ceramic also ensures long-lasting performance and a totally silent operation.

## Quick heat boiler



The Saeco quick heat boiler technology ensures your machine is always ready. Now

you won't have to wait between brewing each espresso, but can prepare coffee after coffee.

## Saves coffee length & strength



You will always get a perfect cup of espresso brewed according to your personal preference, thanks to our memo function which allows you to adjust the coffee length and strength to suit your taste. Enjoy a superb coffee drink in your favorite cup with just the press of a button.

## Adjustable spout



The adjustable spout on our espresso machines will fit every cup and thus prevents the coffee splashing or cooling down while pouring in your cup. This way your espresso is always served at the right temperature while maintaining a clean machine.

## Dishwasher-safe parts



For your convenience, you can put the Saeco's drip tray and milk frother or milk carafe in the dishwasher. This will save time and ensure a hygienic cleaning.

## 5 step adjustable grinders



Different coffee blends require different levels of granularity for the full flavor to unfold. The grind granularity of this espresso machine can be adjusted in 5 settings, from the finest grind, for a full bodied espresso, to the coarsest, for a lighter coffee.



[asimpleswitch.com](http://asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

## Super-automatic espresso machine

Brews 3 coffee varieties Automatic Milk Frother, Silver, 5 step adjustable grinder

HD8750/81

# Specifications

### Design

- Color: Black & silver

### Sustainability

- Power consumption brewing: 1850 W

### Service

- 2-year guarantee

### Finishing

- Material boiler: Stainless steel (Inox)
- Material drip tray: Stainless steel
- Material water tank: Plastic
- Material of main body: Plastic

### Country of origin

- Made in: Europe

### General specifications

- One touch variety: 3
- Grinder settings: 5
- Customizing per drink: Adjustable cup volume
- Ease of use and comfort: Removable drip-tray

- Suitable for: coffee beans
- Ease of cleaning & maintenance: Automatic rinse cycle, Removable brewing group
- Special functions: Automatic milk frother, Ceramic grinder, Pre-brewing

### Technical specifications

- Pump pressure: 15 bar
- Brewing time one cup: 45 (espresso) to 100 (long coffee) sec
- Voltage: 230 V
- Frequency: 50 Hz
- Capacity bean container: 300 gr
- Capacity waste container: 10 servings
- Capacity water tank: 1.5 L
- Cord length: 0.8 m
- Max. cup height: 130 mm
- Water boilers: 1

### Weight and dimensions

- Dimensions of product (WxDxH): 256 x 440 x 340 mm
- Weight of product: 8.0 kg

Issue date 2019-03-28

Version: 7.0.1

© 2019 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)



[asimpleswitch.com](http://asimpleswitch.com)