

PHILIPS

Saeco

Super-automatic
espresso machine

Intelial

Brews 7 coffee varieties

Classic Milk Frother

Black

5 step adjustable grinder



HD8751/11



One touch Espresso and Cappuccino

With ceramic coffee bean grinders for better taste

Only the Saeco Intelial super-automatic espresso machine offers you the perfect Espresso experience, easy to use, easy to customize, easy to clean. Prepare Cappuccino, Latte Macchiato, Espresso or hot water: everything is possible.

Advanced technology designed for coffee perfection

- Fine-tune the coffee's richness with 5 grinder settings
- Extract maximum flavor with the 100% ceramic grinders
- Velvety milk foam with the Classic Milk Frother

High comfort is part of the experience

- The fully removable brewing group can be cleaned in no time



asimpleswitch.com

Highlights

5-steps adjustable grinders



When it comes to the fineness of the grind, this machine never fails to satisfy. Different coffee blends require different levels of granularity for the full flavor to unfold. So the grind granularity of this machine has five adjustable settings – from the finest grind for a full-bodied espresso, to the coarsest for a lighter coffee.

100% Ceramic grinders



The robust 100% ceramic grinders guarantee a moment of pure coffee indulgence for years to come. The ceramic material creates the ideal grind, which allows the water to flow through steadily, extracting the purest essence of the

beans. And unlike other 'regular' grinders, the ceramic material prevents the coffee from overheating and tasting burnt.

Removable brewing group



Efficiency and ease of use were key inspirations when Saeco invented the first brewing group 30 years ago. And to this day, it still proves to be an inspired, resolute piece of technology. As always, it's so simple to clean – just remove it and wash it under the tap for a few seconds, then re-insert it just as easily.

Classic Milk Frother



The Classic Milk Frother is for those who love to assume the role of master craftsman, and it's just easy. Within seconds you can create a rich, silky layer of foam – the crowning glory of your coffee.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Country of origin

Made in: Europe

Service

1-year guarantee

Sustainability

Power consumption brewing: 1900 W

Finishing

Material boiler: Stainless steel (Inox)

Material water tank: Plastic

Material panarello: Plastic

Material of main body: Plastic

Material drip tray: Stainless steel

Material of spout: Plastic

General specifications

One touch variety: 3

Coffee strength settings: 3

Grinder settings: 5

Type of display: LCD

Customizing per drink: Adjustable coffee strength, Adjustable temperature, Adjustable cup volume

Coffee drinks: Espresso, Cappuccino, hot water, Cafè Crème, frothed milk, Espresso Macchiato, Latte Macchiato

Compatible coffee serving: Whole coffee beans, ground coffee powder

Cups at the same time: 2

Type of boiler: Quick heat boiler

Ease of cleaning & maintenance: Automatic rinse cycle, Automatic de-scaling cycle, Removable brewing group, Optional Brita water filter

Special functions: Ceramic grinder, Steam option, Hot water option, Pre-brewing, Manual milk frother Pannarello

Ease of use and comfort: Display, Adjustable spout, Removable drip-tray, Automatic shut-off, Automatic stand-by

Technical specifications

Pump pressure: 15 bar

Brewing time one cup: 45 (espresso) to 100 (long coffee) sec

Voltage: 230 V

Frequency: 50 Hz

Capacity water tank: 1.5 L

Max. cup height: 130 mm

Capacity bean container: 300 gr

Cord length: 0.8 m

Water boilers: 1

Capacity waste container: 10 servings

Weight and dimensions

Dimensions of product (WxDxH): 256 x 440 x 340 mm

Weight of product: 8.9 kg

Design

Color: Black

