

# PHILIPS

## Saeco

Super-automatic  
espresso machine

Intelia

Intelia

Focus



HD8751/13



## Perfect Espresso

has never been so simple

Only Saeco Intelia offers you the perfect Espresso experience. Intelligent and easy to clean

### Perfect espresso

- Pre-brewing function for flavor enhancing
- Save your favorite coffee length and strength

### Grind your favorite coffee beans

- One touch espresso and long coffee
- Ceramic grinders for Aroma preserving

### Easy to use

- Self explanatory color coded user interface
- Wide and bright LED display

### Ease of cleaning and maintaining

- Always a clean machine thanks to auto-clean and descaling
- Easy cleaning thanks to removable brewing group

### Family friendly

- Energy efficient

# Highlights

## Auto cleaning and descaling



Saeco designed this espresso machine to automatically clean its coffee circuit with water upon starting up or switching off of the machine, this delivers a great, fresh taste with each cup of coffee. Regular descaling prolongs your espresso machine's life. This machine will not only prompt when descaling is needed, the automated descaling process will start on your machine and guides you with clear on-screen messages when you have to intervene. Descaling has never been so easy!

## Ceramic grinders

The high-tech grinders of this coffee machine beat the competition's steel grinders on many levels: always perfectly Italian taste because of consistently accurate grinding without overheating, supreme longevity, super-silent operation.

## Energy efficient

This feature keeps the power consumption to a minimum. In fact, less than 1 Watt per hour is needed in stand-by mode, automatic after 1hour, saving resources and money

## Espresso and long coffee



Whether you want to enjoy a an espresso or a long coffee - your favorites are accessible with a touch of a button

## Pre-brewing system

Pre-brewing for even more enjoyment. Thanks to the Pre-brewing Technology, the coffee grounds are moistened before the actual brewing process – ensuring that the aroma can unfold even better.

## Removable brewing group



The brewing group, a Saeco invention, is the heart of our espresso machines, ensuring automation. The brewing group is, depending on the model, easily accessible from the front

or side. It can be removed effortlessly for easily cleaning by rinsing under the tap ensuring maximum hygiene.

## Color coded user interface

Enjoy direct and clear interaction thanks to the self-explanatory icons display. For maximum convenience the icons are colored according to the thraffic light colors: Red requires action, Yellow means the coffee machine is "busy" (like heating up). Green is ready to use.

## Wide and bright LED display

Let the Saeco espresso machine drive your Espresso experience and enjoy direct and clear interaction with it. The customization and maintenance menu allows you to set coffee intensity, descaling cycle guided process, water hardness, water filter installation, Stand-by time and display contrast.

## Saves coffee length & strength



You will always get a perfect cup of espresso brewed according to your personal preference, thanks to our memo function which allows you to adjust the coffee length and strength to suit your taste. Enjoy a superb coffee drink in your favorite cup with just the press of a button.

# Specifications

## Perfect Espresso

**Espresso technology:** Saeco adapting system, Aroma-system: pre-brewing

## Easy to use

**Cleaning and maintenance:** Automatic coffee circuit rinse, Descaling cycle

**Usage:** Adjustable coffee dispenser, Cup holding surface, Rapid steam, Removable brewing group, Normal / long espresso option

## Energy saving

**Energy saving:** Automatic stand-by

## Technical data

**Power:** 1900 W

**Pump Pressure:** 15 bar

## Weight and dimensions

**Product dimensions (L x D x H):** 256x340x440 mm

**Weight:** 8 kg

**Coffee bean capacity:** 300 gr

**Waste container capacity:** 10 servings

## Features

**Hot water / Steam Nozzle**

**Pannarello:** Plastic

**Simultaneous brewing**

**Brita Filter compatible:** Optionable

## Design

**Colour:** Black

**Materials and finishing:** Plastic

## Technical specifications

**Boiler material:** Stainless steel (Inox)

## Water tank

**Water tank capacity:** 1,5 L

