



## Saeco Intelia Super-automatic espresso machine

- Classic Milk Frother
- Black



HD8751/88

# One touch espresso and coffee

With 100% ceramic grinders

Only the Saeco Intelia super-automatic espresso machine offers you the perfect Espresso experience, easy to use, easy to customize, easy to clean. Prepare a tasty Espresso or creamy milk froth with just a touch of a button.

### Authentic Italian coffee perfection

- Delicious milk froth thanks to the classic milk frother
- Coffee without waiting thanks to the quick heat boiler
- Coffee without burnt taste thanks to 100% ceramic grinders

### Set the beverages to suit your taste

- Save your favorite coffee length and strength
- Play with the coffee's richness with our adjustable grinders
- Avoid heat loss and fit every cup with our adjustable spout

### Ease of cleaning and maintaining

- Always a clean machine thanks to auto-clean and descaling
- Easy cleaning thanks to removable brewing group
- Easy cleaning thanks to dishwasher-safe parts



**PHILIPS**

Saeco, a Philips brand

 **Saeco**



# Highlights

## 100% ceramic grinders



This espresso machine is equipped 100% ceramic grinders. Saeco uses ceramic grinders because of their consistent grind without overheating the coffee bean for an impeccable espresso. Ceramic also ensures long-lasting performance and a totally silent operation.

## Quick heat boiler



The Saeco quick heat boiler technology ensures your machine is always ready. Now you won't have to wait between brewing each espresso, but can prepare coffee after coffee.

## Classic milk frother



This Saeco espresso machine comes with the classic milk frother that baristas call a

“Pannarello”. It dispenses steam and is immersed in milk to prepare gorgeous milk foam. Unleash your inner barista by preparing your delicious milk specialties the traditional way!

## Saves coffee length & strength



You will always get a perfect cup of espresso brewed according to your personal preference, thanks to our memo function which allows you to adjust the coffee length and strength to suit your taste. Enjoy a superb coffee drink in your favorite cup with just the press of a button.

## Adjustable spout



The adjustable spout on our espresso machines will fit every cup and thus prevents the coffee splashing or cooling down while pouring in your cup. This way your espresso is always served at the right temperature while maintaining a clean machine.

## Dishwasher-safe parts



For your convenience, you can put the Saeco's drip tray and milk frother or milk carafe in the dishwasher. This will save time and ensure a hygienic cleaning.

## 5 step adjustable grinders



Different coffee blends require different levels of granularity for the full flavor to unfold. The grind granularity of this espresso machine can be adjusted in 5 settings, from the finest grind, for a full bodied espresso, to the coarsest, for a lighter coffee.



## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

# Specifications

## Technical specifications

- Boiler material: Stainless steel (Inox)
- Number of water boilers: 1 boiler
- Water pressure in pump: 15 bar (perfect espresso)
- Supported coffee types: Ground coffee, Whole coffee beans
- Country of origin: Designed in Italy, Made in Europe
- Removable brewing group
- Power: 1900 W
- Voltage: 240 V
- Frequency: 50 Hz
- Cord length: 80 cm

## Sustainability

- Automatic Stand-by Option

## Perfect Espresso

- Espresso technology: Saeco adapting system, Aroma-system: pre-brewing

## Finishing

- Material panarello: Plastic

## Service

- 2-year worldwide guarantee

## Easy to use

- Cleaning and maintenance: Automatic coffee circuit rinse, Descaling cycle
- Usage: Adjustable coffee dispenser, Cup holding surface, Rapid steam, Removable brewing group, Normal / long espresso option

## Weight and dimensions

- Product weight: 8.9 kg
- Product dimensions (L x D x H): 256 x 340 x 440 mm
- Coffee bean capacity: 300 gr
- Waste container capacity: 10 servings
- Water tank capacity: 1.5 l
- Maximum cup height: 130 mm

## Features

- Hot water / Steam Nozzle
- Pannarello: Plastic
- Simultaneous brewing
- Brita Filter compatible: Optionable

## Design

- Colour: Black
- Materials and finishing: Plastic

