

PHILIPS

Saeco

Super-automatic
espresso machine

Intelial

Brews 7 coffee varieties

Automatic Milk Frother

Stainless steel

HD8752/87



One touch espresso and milk froth With Saeco's ultimate cappuccinatore

Only the Saeco Intelial super-automatic espresso machine offers you the perfect Espresso experience, easy to use, easy to customize, easy to clean. Prepare a tasty Espresso or creamy milk froth with just a touch of a button.

Authentic Italian coffee perfection

- Delicious milk froth thanks to the automatic milk frother
- Coffee without waiting thanks to the quick heat boiler
- Coffee without burnt taste thanks to 100% ceramic grinders

Set the beverages to suit your taste

- Save your favorite coffee settings
- Play with the coffee's richness with our adjustable grinders
- Avoid heat loss and fit every cup with our adjustable spout

Ease of cleaning and maintaining

- Always a clean machine thanks to auto-clean and descaling
- Easy cleaning thanks to removable brewing group
- Easy cleaning thanks to dishwasher-safe parts
- Cutting-edge design with stainless steel finish

Highlights

Stainless steel



The cutting-edge design of your Saeco espresso machine is rounded off by the stainless steel finish. The stainless steel provides a high quality look and will be a highlight on your kitchen counter tops. It also gives greater resistance for a long-lasting performance.

100% ceramic grinders



This espresso machine is equipped 100% ceramic grinders. Saeco uses ceramic grinders because of their consistent grind without overheating the coffee bean for an impeccable espresso. Ceramic also ensures long-lasting performance and a totally silent operation.

Quick heat boiler



The Saeco quick heat boiler technology ensures your machine is always ready. Now you won't have to wait between brewing each espresso, but can prepare coffee after coffee.

Saves your coffee settings



You will always get a perfect cup of espresso brewed just for you, according to your personal preference, thanks to our innovative memo function to adjust the coffee length, strength and temperature. Enjoy a superb coffee drink in your favorite cup with just the press of a button.

Adjustable spout



The adjustable spout on our espresso machines will fit every cup and thus prevents the coffee splashing or cooling down while pouring in your cup. This way your espresso is always served at the right temperature while maintaining a clean machine.

Dishwasher-safe parts




For your convenience, you can put the Saeco's drip tray and milk frother or milk carafe in the dishwasher. This will save time and ensure a hygienic cleaning.

5 step adjustable grinders



Different coffee blends require different levels of granularity for the full flavor to unfold. The grind granularity of this espresso machine can be adjusted in 5 settings, from the finest grind, for a full bodied espresso, to the coarsest, for a lighter coffee.

Removable brewing group



The brewing group, a Saeco invention, is the heart of our espresso machines, ensuring automation. The brewing group is, depending on the model, easily accessible from the front or side. It can be removed effortlessly for easily cleaning by rinsing under the tap ensuring maximum hygiene.

Specifications

Perfect Espresso

Espresso technology: Saeco adapting system, Aroma-system: pre-brewing

Technical specifications

Supported coffee types: Ground coffee, Whole coffee beans

Water pressure in pump: 15 bar (perfect espresso)

Removable brewing group

Country of origin: Designed in Italy, Made in Europe

Cord length: 80 cm

Number of water boilers: 1 boiler

Power: 1850 W

Boiler material: Stainless steel (Inox)

Easy to use

Cleaning and maintenance: Automatic coffee circuit rinse, Descaling cycle

Usage: Adjustable coffee dispenser, Cup holding surface, Rapid steam, Removable brewing group, Normal / long espresso option

Weight and dimensions

Product weight: 8.9 kg

Water tank capacity: 1.5 L

Maximum cup height: 130 mm

Product dimensions (L x D x H): 256 x 340 x 440 mm

Coffee bean capacity: 300 gr

Waste container capacity: 10 servings

Features

Cappuccinatore

Hot water / Steam Nozzle

Simultaneous brewing

Brita Filter compatible: Optionable, Yes

Design

Colour: Stainless Steel/Black

Materials and finishing: Stainless Steel/Plastic

Energy saving

Energy saving: Automatic stand-by

Service

1-year guarantee

