

PHILIPS

Saeco

Super-automatic
espresso machine

Intelìa

Brews 7 coffee varieties

Integrated milk jug & frother

Stainless steel

HD8753/87



One touch Espresso and Cappuccino

With Saeco's latest Latte Perfetto technology

Only the Saeco Intelìa super-automatic espresso machine offers you the perfect Espresso experience, easy to use, easy to customize, easy to clean. Prepare perfect Cappuccino or Espresso with just a touch of a button.

Authentic Italian coffee perfection

- Perfect froth thanks to the dual chamber milk carafe
- Coffee without waiting thanks to the quick heat boiler
- Coffee without burnt taste thanks to 100% ceramic grinders

Set the beverages to suit your taste

- Save your favorite coffee settings
- Play with the coffee's richness with our adjustable grinders
- Avoid heat loss and fit every cup with our adjustable spout

Ease of cleaning and maintaining

- Always a clean machine thanks to auto-clean and descaling
- Easy cleaning thanks to removable brewing group
- Easy cleaning thanks to dishwasher-safe parts
- Cutting-edge design with stainless steel finish



asimpleswitch.com

Highlights

Stainless steel



The cutting-edge design of your Saeco espresso machine is rounded off by the stainless steel finish. The stainless steel provides a high quality look and will be a highlight on your kitchen counter tops. It also gives greater resistance for a long-lasting performance.

100% ceramic grinders



This espresso machine is equipped 100% ceramic grinders. Saeco uses ceramic grinders because of their consistent grind without overheating the coffee bean for an impeccable espresso. Ceramic also ensures long-lasting performance and a totally silent operation.

Quick heat boiler



The Saeco quick heat boiler technology ensures your machine is always ready. Now you won't have to wait between brewing each espresso, but can prepare coffee after coffee.

Dual chamber milk carafe



Enjoy your milk specialties fully automated with the patented milk carafe with dual chamber technology. Simply pour milk into the carafe, plug it into the machine and select your coffee drink. With the dual chamber technology you will always enjoy professional coffee drinks with dense, long-lasting milk froth at the ideal temperature from a constant splash-free flow of milk.

Saves your coffee settings



You will always get a perfect cup of espresso brewed just for you, according to your personal preference, thanks to our innovative memo function to adjust the coffee length, strength and temperature. Enjoy a superb coffee drink in your favorite cup with just the press of a button.

Adjustable spout



The adjustable spout on our espresso machines will fit every cup and thus prevents the coffee splashing or cooling down while pouring in your cup. This way your espresso is always served at the right temperature while maintaining a clean machine.

Dishwasher-safe parts



For your convenience, you can put the Saeco's drip tray and milk frother or milk carafe in the dishwasher. This will save time and ensure a hygienic cleaning.

5 step adjustable grinders



Different coffee blends require different levels of granularity for the full flavor to unfold. The grind granularity of this espresso machine can be adjusted in 5 settings, from the finest grind, for a full bodied espresso, to the coarsest, for a lighter coffee.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Perfect Espresso

Espresso technology: Saeco adapting system, Aroma-system: pre-brewing

Technical specifications

Supported coffee types: Ground coffee, Whole coffee beans

Water pressure in pump: 15 bar (perfect espresso)

Removable brewing group

Country of origin: Designed in Italy, Made in Europe

Cord length: 80 cm

Number of water boilers: 1 boiler

Power: 1900 W

Boiler material: Stainless steel (Inox)

Easy to use

Cleaning and maintenance: Automatic coffee circuit rinse, Descaling cycle

Usage: Adjustable coffee dispenser, Cup holding surface, Rapid steam, Removable brewing group, Normal / long espresso option

Weight and dimensions

Product weight: 8.9 kg

Water tank capacity: 1.5 L

Maximum cup height: 130 mm

Milk carafe capacity: 0.5 L

Product dimensions (L x D x H): 256 x 340 x 444 mm

Coffee bean capacity: 300 gr

Waste container capacity: 10 servings

Features

Simultaneous brewing

Brita Filter compatible: Optionable

Hot water wand

Design

Colour: Black and steel

Materials and finishing: Frontal Stainless steel, stainless steel grid, stainless steel cup holder

Energy saving

Energy saving: Automatic stand-by

Service

1-year guarantee

