



Saeco Intelia Deluxe Super-automatic espresso machine

- 4 Beverages
- Automatic Milk Frother
- Stainless Steel

HD8759/47



The quality you demand, the ease of use you expect

A timeless design Made in Italy

Saeco presents Intelia Deluxe. A smartly crafted piece of technology delivering proven quality, convenience, and divine coffee. Housed in a stainless steel body with a timeless design, Intelia is an ambassador of Italian craftsmanship.

Any coffee for any moment

- Enjoy 4 beverages at your fingertips
- Velvety froth at one touch with the Automatic Milk Frother
- Adjust the length, 5 aroma strength and 10 grinder settings
- Adjust and store your personal user profile

Every coffee crafted to perfection

- 20,000 cups of finest coffee with durable ceramic grinders
- Perfect milk foam thanks to Latte Perfetto technology
- Iconic stainless steel finishing, shaped to precision
- Hot coffee from the first cup with Thermoblock


Attentive and anticipating at your command

- Smartly designed to fit any kitchen countertop
- Enjoy a great coffee with Auto-Rinse & guided descaling
- Thorough cleaning thanks to fully removable brewing group

PHILIPS

Saeco, a Philips brand

 **Saeco**



Highlights

100% ceramic grinders



Our grinders are made of high-tech ceramic: exceptionally hard and precise. Fresh beans are gently ground, without risk of overheating: extracting all the best flavors and aroma, delivering a superior coffee taste for at least 20,000 cups.

4 beverages



Enjoy your favourite drinks for your special moments. Whether you crave for an espresso, a coffee or a milk based recipe, your Super-automatic machine delivers a perfect in-cup result with no hassle and in no time!

Automatic Milk Frother



Preparing a velvety cappuccino is easy thanks to the Automatic Milk Frother. The milk frother, which baristas also call

“cappuccinatore”, will draw the milk directly from a carton or jug, froth it automatically and dispensing it into your cup with a constant flow of milk without any splashing.

Auto-Rinse & Guided descaling



This espresso machine automatically cleans its coffee circuit with water upon starting up or switching off of the machine, this delivers a great, fresh taste with each cup of coffee. Regular descaling prolongs your espresso machine's life. This machine will prompt when descaling is needed. It will guide you with on-screen messages what you have to do and when.

Customize your coffees



This Super-Automatic machine offers an abundance of indulgent options to customize your beverage to your taste. You can easily personalize and memorize length, strength and temperature for each drink. Feel free to explore, experiment and dream up any drink!

Front loading for easy access



Your super-automatic espresso machine is effortless to use thanks to the frontal loading of the water tank and the dump box.

Latte Perfetto Technology



Every coffee you prepare will be topped with a silky, milk layer that beckons the taste buds. The milk carafe froths the milk twice, then pours a splash free creamy layer into your cup at just the right temperature. The carafe can also be stored conveniently in the fridge and it is incredibly hygienic.

Thermoblock



Say goodbye to lukewarm coffee. Thermoblock ensures a hot coffee and cappuccino for you family from the first cup, in no time. The secret is in its light aluminum and stainless steel body, which can reach hot temperatures, fast.

Specifications

Customization

- Aroma Strength Settings: 5
- Coffee and Milk Length: Adjustable
- Grinder Settings: 5
- Pre Brew Aroma control: No
- Temperature settings: 3
- User Profiles: 1

Other features

- Auto-Rinse & Guided descaling
- Main Switch ON / OFF button: No
- Quick Heat Boiler
- Removable brew group

Technical specifications

- Capacity waste container: 10 servings
- Coffee bean capacity: 300 g
- Color & Finishing: Stainless Steel
- Cord length: >100 cm
- Country of origin: Italy
- Filter compatibility: Brita Intenza

- Frequency: 50 Hz
- Max. cup height: 115 mm
- Voltage: 120 V
- Waste container: Frontal access
- Water tank: Frontal access
- Weight of product: 8.9 kg
- Product dimensions: 256 x 340 x 444 mm
- Capacity water tank: 1.8 L

Variety

- Beverages: Espresso, Espresso Lungo, Hot water, Milk froth
- Coffee Powder Option
- Double Cup
- Milk Double Cup: No

General specifications

- User Interface: Basic Display

Service

- 1-year guarantee