



**Saeco Minuto
Super-automatic
espresso machine**

- Brews 7 coffee varieties
- Classic Milk Frother
- Black
- 5 step adjustable grinder



HD8761/01

Always your favorite coffee at just one touch

With the one-click removable brewing group

Only the Saeco Minuto super-automatic espresso machine delivers the real first bean to cup experience with maximum convenience, top-notch performance and large capacities in extra compact dimensions

Advanced technology designed for coffee perfection

- Fine-tune the coffee's richness with 5 grinder settings
- Extract maximum flavor with the 100% ceramic grinders
- Velvety milk foam with the Classic Milk Frother

High comfort is part of the experience

- The fully removable brewing group can be cleaned in no time

PHILIPS

Saeco, a Philips brand

 **Saeco**



Highlights

5-steps adjustable grinders



When it comes to the fineness of the grind, this machine never fails to satisfy. Different coffee blends require different levels of granularity for the full flavor to unfold. So the grind granularity of this machine has five adjustable settings - from the finest grind for a full-bodied espresso, to the coarsest for a lighter coffee.

100% Ceramic grinders



The robust 100% ceramic grinders guarantee a moment of pure coffee indulgence for years to come. The ceramic material creates the ideal grind, which allows the water to flow through steadily, extracting the purest essence of the beans. And unlike other 'regular' grinders, the ceramic material

prevents the coffee from overheating and tasting burnt.

Removable brewing group



Efficiency and ease of use were key inspirations when Saeco invented the first brewing group 30 years ago. And to this day, it still proves to be an inspired, resolute piece of technology. As always, it's so simple to clean – just remove it and wash it under the tap for a few seconds, then re-insert it just as easily.

Classic Milk Frother



The Classic Milk Frother is for those who love to assume the role of master craftsman, and it's just easy. Within seconds you can create a rich, silky layer of foam - the crowning glory of your coffee.

Specifications

Country of origin

- Made in: Europe

Sustainability

- Power consumption brewing: 1850 W

Finishing

- Material boiler: Stainless steel (Inox)
- Material of main body: Plastic
- Material panarello: Plastic
- Material water tank: Plastic
- Material drip tray: Stainless steel
- Material of spout: Plastic

Service

- 2-year guarantee

General specifications

- One touch variety: 3
- Coffee strength settings: 5
- Grinder settings: 5
- Type of display: LCD
- Customizing per drink: Adjustable coffee strength, Adjustable cup volume
- Coffee drinks: Espresso, Cappuccino, hot water, Café Crème, frothed milk, Espresso Macchiato, Latte Macchiato
- Compatible coffee serving: Whole coffee beans, ground coffee powder
- Cups at the same time: 2
- Ease of use and comfort: Display, Adjustable spout, Removable drip-tray
- Type of boiler: Quick heat boiler
- Special functions: Ceramic grinder, Pre-brewing, Manual milk frother Pannarello
- Ease of cleaning & maintenance: Automatic descaling cycle, Removable brewing group, Automatic rinse cycle, Optional Brita water filter

Technical specifications

- Pump pressure: 15 bar
- Brewing time one cup: 45 (espresso) to 100 (long coffee) sec
- Capacity water tank: 1.8 L
- Max. cup height: 152 mm
- Capacity bean container: 250 gr
- Cord length: 0.8 m
- Water boilers: 1
- Capacity waste container: 15 servings
- Frequency: 50 Hz
- Voltage: 230 V

Weight and dimensions

- Dimensions of product (WxDxH): 215 x 429 x 330 mm
- Weight of product: 7.5 kg

Design

- Color: Black

