



**Saeco Minuto  
Super-automatic  
espresso machine**

- Brews 7 coffee varieties
- Classic Milk Frother
- Black
- 5-step adjustable grinder



**HD8761/18**

Always your favourite coffee with just one touch

With the one-click removable brewing group

Only the Saeco Minuto super-automatic espresso machine delivers the first real bean-to-cup experience with maximum convenience, top-notch performance and large capacities in extra-compact dimensions

**Authentic Italian coffee perfection**

- Delicious milk froth thanks to the classic milk frother
- Coffee without waiting thanks to the quick-heat boiler
- Coffee without burnt taste thanks to 100% ceramic grinders

**Set the beverages to suit your taste**

- Save your favourite coffee length and strength
- Play with the coffee's richness with our adjustable grinders
- Avoid heat loss and fit every cup with our adjustable spout

**Easy to clean and maintain**

- Always a clean machine thanks to auto-clean and descaling
- Easy cleaning thanks to removable brewing group
- Easy cleaning thanks to dishwasher-safe parts

 **Saeco**

**PHILIPS**

Saeco, a Philips brand



# Highlights

## 100% ceramic grinders



This espresso machine is equipped with 100% ceramic grinders. Saeco uses ceramic grinders because of their consistent grind without overheating the coffee bean, for an impeccable espresso. Ceramic also ensures long-lasting performance and totally silent operation.

## Quick-heat boiler



The Saeco quick-heat boiler technology ensures your machine is always ready. Now you won't have to wait between brewing each espresso, but can prepare coffee after coffee.

## Classic milk frother



This Saeco espresso machine comes with the classic milk frother that baristas call a

“Pannarello”. It dispenses steam and is immersed in milk to prepare gorgeous milk foam. Unleash your inner barista by preparing your delicious milk specialties the traditional way!

## Saves coffee length and strength



You will always get a perfect cup of espresso brewed according to your personal preference thanks to our memo function, which allows you to adjust the coffee length and strength to suit your taste. Enjoy a superb coffee drink in your favourite cup at the touch of a button.

## Adjustable spout



The adjustable spout on our espresso machines will fit every cup and thus prevent the coffee splashing or cooling down while being poured into your cup. This way your espresso is always served at the right temperature, while the machine is kept clean.

## Dishwasher-safe parts



For your convenience, you can put the Saeco's drip tray and milk frother or milk carafe in the dishwasher. This will save time and ensure a hygienic clean.

## 5-step adjustable grinders



Different coffee blends require different levels of granularity for the full flavour to unfold. The grind granularity of this espresso machine can be adjusted in 5 settings, from the finest grind, for a full-bodied espresso, to the coarsest, for a lighter coffee.



[asimpleswitch.com](http://asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas — Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

# Specifications

## Technical specifications

- Number of water boilers: 1 boiler
- Water pressure in pump: 15 bar (perfect espresso)
- Supported coffee types: Ground coffee, Whole coffee beans
- Country of origin: Designed in Italy, Made in Europe
- Removable brewing group
- Power: 1850 W
- Voltage: 240 V
- Frequency: 50 Hz
- Cord length: 80 cm

## Perfect Espresso

- Espresso technology: Saeco adapting system, Aroma-system: pre-brewing

## Service

- 2-year worldwide guarantee

## Easy to use

- Cleaning and maintenance: Descaling cycle
- Usage: Adjustable coffee dispenser, Rapid steam, Removable brewing group, Normal/long espresso option

## Weight and dimensions

- Water tank capacity: 1.8 l
- Maximum cup height: 152 mm
- Product weight: 7.5 kg
- Product dimensions (L x D x H): 215 x 429 x 330 mm
- Coffee bean capacity: 250 gr
- Waste container capacity: 15 servings

## Features

- Simultaneous brewing
- Brita Filter compatible: Optional

## Design

- Colour: Matt Black
- Materials and finishing: Plastic

