



Saeco Minuto
Super-automatic
espresso machine

- Brews 3 coffee varieties
- Classic Milk Frother
- Black
- 5 step adjustable grinder



HD8765/47



Always your favorite coffee at just one touch

With the one-click removable brewing group

Only the Saeco Minuto super-automatic espresso machine delivers the real first bean to cup experience with maximum convenience, top-notch performance and large capacities in extra compact dimensions

Advanced technology designed for coffee perfection

- Fine-tune the coffee's richness with 5 grinder settings
- Velvety milk foam with the Classic Milk Frother

High comfort is part of the experience

- The fully removable brewing group can be cleaned in no time

Ease of cleaning and maintaining

- Always a clean machine thanks to auto-clean and descaling
- Easy cleaning thanks to dishwasher-safe drip tray

PHILIPS

Saeco, a Philips brand

 **Saeco**



Highlights

Auto cleaning and descaling



Saeco designed this espresso machine to automatically clean its coffee circuit with water upon starting up or switching off of the machine, this delivers a great, fresh taste with each cup of coffee. Regular descaling prolongs your espresso machine's life. This machine will not only prompt when descaling is needed, the automated descaling process will start on your machine and guides you with clear on-screen messages when you have to intervene. Descaling has never been so easy!

Dishwasher-safe drip tray



For your convenience, you can wash the drip tray of your Saeco in the dishwasher. This will save time and ensure a hygienic cleaning.

5-steps adjustable grinders



When it comes to the fineness of the grind, this machine never fails to satisfy. Different coffee blends

require different levels of granularity for the full flavor to unfold. So the grind granularity of this machine has five adjustable settings - from the finest grind for a full-bodied espresso, to the coarsest for a lighter coffee.

Removable brewing group



Efficiency and ease of use were key inspirations when Saeco invented the first brewing group 30 years ago. And to this day, it still proves to be an inspired, resolute piece of technology. As always, it's so simple to clean - just remove it and wash it under the tap for a few seconds, then re-insert it just as easily.

Classic Milk Frother



The Classic Milk Frother is for those who love to assume the role of master craftsman, and it's just easy. Within seconds you can create a rich, silky layer of foam - the crowning glory of your coffee.

Specifications

Service

- 1-year guarantee

Design

- Color: Black

Finishing

- Material drip tray: Stainless steel
- Material panarello: Stainless steel
- Material water tank: Plastic
- Material boiler: Stainless steel (Inox)
- Material of main body: Plastic

Country of origin

- Made in: Europe

General specifications

- Coffee drinks: Espresso, Café Crème
- Suitable for: Whole coffee beans, ground coffee powder
- Cups at the same time: 2
- Customizing per drink: Adjustable cup volume
- Ease of cleaning & maintenance: Automatic descaling cycle, Optional Brita water filter, Removable brewing group, Dishwasher-safe parts, Automatic rinse cycle
- Ease of use and comfort: Automatic shut-off, Display, Adjustable spout, Automatic stand-by, Removable drip-tray, Removable water tank
- Special functions: Manual milk frother Pannarello, Ceramic grinder, CoffeeSwitch, Pre-brewing, Hot water option, Steam option
- Type of boiler: Quick heat boiler

Sustainability

- Power consumption brewing: 1850 W

Technical specifications

- Capacity bean container: 250 gr
- Capacity waste container: 15 servings
- Capacity water tank: 1.8 L
- Cord length: 0.8 m
- Frequency: 60 Hz
- Max. cup height: 152 mm
- Voltage: 120 V
- Water boilers: 1
- Pump pressure: 15 bar

Weight and dimensions

- Dimensions of product (WxDxH): 215 x 429 x 330 mm
- Weight of product: 8.5 kg