



**Saeco Minuto  
Super-automatic  
espresso machine**

- Brews 7 coffee varieties
- Automatic Milk Frother
- Silver
- 5 step adjustable grinder



HD8772/47

Always your favorite coffee at just one touch

With the one-click removable brewing group

Only the Saeco Minuto super-automatic espresso machine delivers the real first bean to cup experience with maximum convenience, top-notch performances and large capacities in extra compact dimensions

**Advanced technology designed for coffee perfection**

- Fine-tune the coffee's richness with 5 grinder settings
- Extract maximum flavor with the 100% ceramic grinders

**High comfort is part of the experience**

- The fully removable brewing group can be cleaned in no time

**A variety of coffees customized to your taste**

- The strength selection remembers just how strong you like it

**PHILIPS**

Saeco, a Philips brand

 **Saeco**



# Highlights

## 5-steps adjustable grinders



When it comes to the fineness of the grind, this machine never fails to satisfy. Different coffee blends require different levels of granularity for the full flavor to unfold. So the grind granularity of this machine has five adjustable settings - from the finest grind for a full-bodied espresso, to the coarsest for a lighter coffee.

## 100% Ceramic grinders



The robust 100% ceramic grinders guarantee a moment of pure coffee indulgence for years to come. The ceramic material creates the ideal grind, which allows the water to flow through steadily, extracting the purest essence of the beans. And unlike other 'regular' grinders, the ceramic material prevents the coffee from overheating and tasting burnt.

## Removable brewing group



Efficiency and ease of use were key inspirations when Saeco invented the first brewing group 30 years ago. And to this day, it still proves to be an inspired, resolute piece of technology. As always, it's so simple to clean – just remove it and wash it under the tap for a few seconds, then re-insert it just as easily.

## Memo Function



Once you've chosen your ideal strength from the 5 different settings, you can easily save it with the Memo Function, as well your desired length and temperature. Then every cup in the future will be customised exactly to your taste. You'll never have to remind it again, unlike the local barista.

# Specifications

## Weight and dimensions

- Dimensions of product (WxDxH): 215 x 429 x 330 mm
- Weight of product: 8.9 kg

## Service

- 1-year guarantee

## Design

- Color: Silver, Black

## Country of origin

- Made in: Europe

## Technical specifications

- Pump pressure: 15 bar
- Frequency: 60 Hz
- Voltage: 120 V
- Capacity bean container: 250 gr
- Capacity waste container: 15 servings
- Capacity water tank: 1.8 L
- Cord length: 0.8 m
- Max. cup height: 152 mm
- Water boilers: 1
- Pump pressure: 15 bar

## Finishing

- Material drip tray: Stainless steel
- Material water tank: Plastic
- Material boiler: Stainless steel (Inox)
- Material of main body: Plastic

## General specifications

- Type of display: LCD
- Coffee drinks: Espresso, Cappuccino, hot water, Café Crème, frothed milk, Espresso Macchiato, Latte Macchiato
- Suitable for: Whole coffee beans, ground coffee powder
- Cups at the same time: 2
- Ease of cleaning & maintenance: Automatic descaling cycle, Removable brewing group, Optional Brita water filter, Dishwasher-safe parts, Automatic rinse cycle
- Ease of use and comfort: Automatic shut-off, Display, Automatic stand-by, Adjustable spout, Removable drip-tray, Removable water tank
- Special functions: Automatic milk frother, Ceramic grinder, Pre-brewing, CoffeeSwitch
- Customizing per drink: Adjustable coffee strength, Adjustable cup volume, Adjustable temperature
- Type of boiler: Quick heat boiler

## Sustainability

- Power consumption brewing: 1900 W