



**Saeco Minuto  
Super-automatic  
espresso machine**

- Brews 3 coffee varieties
- Classic Milk Frother
- Black
- 5 step adjustable grinder



HD8775/48

Always your favorite coffee at just one touch

With the one-click removable brewing group

Only the Saeco Minuto super-automatic espresso machine delivers the real first bean to cup experience with maximum convenience, top-notch performances and large capacities in extra compact dimensions

**Authentic Italian coffee perfection**

- Filter coffee and espresso from one machine

**Advanced technology designed for coffee perfection**

- Extract maximum flavor with the 100% ceramic grinders
- Fine-tune the coffee's richness with 5 grinder settings

**High comfort is part of the experience**

- The fully removable brewing group can be cleaned in no time

**PHILIPS**

Saeco, a Philips brand

 **Saeco**



## Highlights

### Saeco's dual pressure lever



Enjoy both coffee and espresso from your favorite whole beans in a single, compact machine thanks to Saeco's new dual pressure lever. Simply turn the dual pressure lever to one side to brew a filter coffee with low water pressure. Or move the lever to the other side and prepare a real Italian espresso with 15 bar water pressure.

### 5-steps adjustable grinders



When it comes to the fineness of the grind, this machine never fails to satisfy. Different coffee blends require different levels of granularity for the full flavor to unfold. So the grind granularity of this machine has five adjustable settings - from the finest grind for a full-bodied espresso, to the coarsest for a lighter coffee.

### Removable brewing group



Efficiency and ease of use were key inspirations when Saeco invented the first brewing group 30 years ago. And to this day, it still proves to be an inspired, resolute piece of technology. As always, it's so simple to clean – just remove it and wash it under the tap for a few seconds, then re-insert it just as easily.

### 100% Ceramic grinders



The robust 100% ceramic grinders guarantee a moment of pure coffee indulgence for years to come. The ceramic material creates the ideal grind, which allows the water to flow through steadily, extracting the purest essence of the beans. And unlike other 'regular' grinders, the ceramic material prevents the coffee from overheating and tasting burnt.

## Specifications

### Weight and dimensions

- Weight incl. packaging: 7.5 kg

### Service

- 1-year guarantee

### Technical specifications

- Brewing time one cup: 45 (espresso) to 100 (long coffee) sec
- Frequency: 60 Hz
- Voltage: 120 V
- Capacity waste container: 15 servings
- Capacity water tank: 1.8 L
- Max. cup height: 152 mm
- Water boilers: 1
- Coffee bean capacity: 250 g
- Color & Finishing: Black
- Cord length: 80 cm
- Country of origin: Made in Europe
- Filter compatibility: Brita Intenza
- Product dimensions: 215 x 429 x 330 mm

### Finishing

- Material drip tray: Stainless steel
- Material panarello: Plastic
- Material water tank: Plastic
- Material boiler: Stainless steel (Inox)

### General specifications

- One touch variety: 7
- Coffee strength settings: 5
- Temperature settings: 3
- Grinder settings: 5
- Type of display: LCD
- Coffee drinks: Espresso, Café Crème
- Suitable for: Whole coffee beans, ground coffee powder
- Cups at the same time: 2
- Type of boiler: Quick heat boiler
- Customizing per drink: Adjustable temperature, Adjustable coffee strength, Adjustable cup volume
- Milk Solution: Classic Milk Frother

### Sustainability

- Power consumption brewing: 1400 W

### Variety

- Beverages: Espresso
- Coffee Switch