

PHILIPS

Super-automatic
espresso machine

3100 series

Brews 5 coffee varieties

Integrated milk jug & frother

Black

5-step adjustable grinder



HD8828/01



One touch espresso and cappuccino exactly
your way

With our intuitive display

Get your perfect espresso and cappuccino from fresh beans thanks to the 100% ceramic grinders and select strength, temperature and length via the intuitive display. Your hot cappuccino is a one-touch job, thanks to the Integrated milk jug.

Any coffee for any moment

- Espresso from fresh beans at the touch of a button
- One-touch creamy cappuccinos with the integrated milk carafe

Your fresh coffee experience

- 20,000 cups of finest coffee with durable ceramic grinders
- Adjustable grinding settings for your preferred taste
- Customize your coffee with the coffee strength selection

Easy to use

- Easily operate your machine via the Intuitive display
- Fits your cup thanks to the adjustable coffee spout

Easy to clean and maintain

- Delight without hassle: high capacity in a compact design
- Easy cleaning thanks to the fully removable brewing group
- Auto-cleaning cycle & descaling program

Highlights

One touch espresso from beans



You can get a perfectly brewed espresso, or two at once, right in your cup from freshly ground beans by simply pushing a button and waiting a few seconds.

Integrated milk carafe



Enjoy super creamy cappuccinos at the perfect temperature, in the easiest way possible. Simply pour milk into the carafe, plug it into the machine, and select your preferred beverage. Whether it's a cappuccino or frothed milk, your drink will be served within seconds, with a splash-free flow at the ideal temperature.

100% ceramic grinders




Our grinders are 100% pure ceramic: extremely hard and precise, so you can enjoy fresh aromatic coffee, for at least 20.000 cups.

Adjustable grinding settings




You can adjust the granularity of the grinders at 5 different levels. Choose the finest grinding for a full bodied espresso, all the way up to the coarsest for a lighter coffee, all according to your preferred taste.

Customize your coffee




You will always get a perfect cup of coffee brewed to your personal preference thanks to the temperature, length and strength selection. Moreover, the memo function allows you to save the coffee length for each drink. Enjoy a superb coffee in your favorite cup, all at the touch of a button.

Intuitive Display




The intuitive display shows you all relevant information to easily interact with your machine and get the best performance. The buttons on the front panel offer you a selection of one-touch beverages ready at your fingertips.

Adjustable coffee spout



No matter the size of your favorite glass or cup, with one movement the coffee spout adjusts so that all the aromas are preserved and your coffee stays perfectly hot, right in your cup. At its highest position the spout can even fit a 5.9 in. (15 cm) latte macchiato glass.

High capacity & compact design



Enjoy more room and go longer without refill thanks to the high-capacity bean, water, and waste containers in a super-compact design. This smart, fully automatic machine provides you with maximum convenience, top notch performance, and large capacities (a 60.8 oz. (1.8 l) water tank, 16.9 oz. (0.5 l) milk carafe, 0.5 lb (250 g) bean container, and a waste container capacity of up to 15 servings).

Fully removable brewing group



The brewing group is the heart of every fully automatic coffee machine, and should be cleaned once a week. Our brewing group is easily accessible from the side, and can be removed with just one click for easy washing under the tap.

Specifications

Country of origin

Made in: Romania

General specifications

Ease of cleaning & maintenance: Optional

Brita water filter, Removable brewing group

Special functions: Hot water option, Integrated carafe, Pre-brewing, Ceramic grinder

Ease of use and comfort: Removable spout, Removable water tank

Coffee drinks: Espresso

Coffee strength settings: 5

Suitable for: Whole coffee beans, ground coffee powder

Customizing per drink: Adjustable coffee strength, Adjustable cup volume, Adjustable temperature

Grinder settings: 5

One touch variety: 5

Temperature settings: 3

Type of boiler: Stainless steel boiler

Type of carafe: Basic carafe

Type of display: LCD

Service

2-year guarantee

Sustainability

ECO setting

Power consumption brewing: 1850 W

Technical specifications

Frequency: 50 Hz

Voltage: 230 V

Capacity bean container: 250 gr

Capacity waste container: 15 servings

Capacity water tank: 1,8 L

Cord length: 0,8 m

Max. cup height: 152 mm

Pump pressure: 15 bar

Water boilers: 1

Brewing time one cup: 45 (espresso) to 100 (long coffee) sec

Capacity milk carafe: 500 L

Weight and dimensions

Dimensions of product (WxDxH):

215x429x330 mm

Weight of product: 7,2 kg

Design

Color: Black

Finishing

Material boiler: Stainless steel (Inox)

Material of main body: Plastic

