

# PHILIPS

Super-automatic  
espresso machine

3000 Series

5 Beverages

Easy Cappuccino System

Silver

HD8829/15



## Your favorite cappuccino, just one touch away With high capacities in a compact size

With the Philips 3000 Series Easy Cappuccino, your favorite Cappuccino is just a one touch job. Thanks to its high capacity in a compact design, you can enjoy espresso, coffee and cappuccino from fresh beans at the touch of a button.

### **A variety of coffees customized to your taste**

- Enjoy 5 coffees at your fingertips, including cappuccino
- Preparing your cappuccino has never been easier
- Adjust the length, 2 aroma strength and 5 grinder settings

### **Your fresh coffee experience**

- 20,000 cups of finest coffee with durable ceramic grinders
- Adjust your coffee spout to fit any cup
- Coffee at the perfect temperature with our Thermoblock

### **Enjoy your coffees every day with no hassle**

- Clean milk residues after every use with milk clean function
- External milk container included, easy to clean and store
- Designed to maximize capacities in a compact footprint
- Enjoy a great coffee with Auto-Rinse & guided descaling
- Easy cleaning thanks to fully removable brew group

# Highlights

## External milk container



Enjoy your creamy cappuccino with the milk you prefer thanks to the external milk container, dishwasher safe. Easily unplug it from the machine and put it in the fridge for long lasting freshness. Cappuccino with every kind of milk has never been so easy.

## 100% ceramic grinders



Our grinders are 100% pure ceramic: extremely hard and precise, so you can enjoy fresh aromatic coffee, for at least 20.000 cups.

## 5 aromatic coffees



Enjoy your favourite coffees for your special moments. Whether you crave for an espresso, a coffee or a milk based recipe, your fully-automatic espresso machine delivers a perfect in-cup result with no hassle and in no time!

## Adjustable coffee spout



The adjustable spout on our espresso machines will fit every cup and thus prevents the coffee splashing or cooling down while pouring in your cup. This way your espresso is always served at the right temperature while maintaining a clean machine.

## Customize your coffees




This Super-Automatic machine offers an abundance of indulgent options to customize your beverage to your taste. You can easily personalize and memorize length and strength for each drink. Feel free to explore, experiment and dream up any drink!

## Easy Cappuccino System



You can get a perfectly brewed espresso right in your cup from freshly ground beans, simply push a button and wait a few seconds. Now, with the new Easy Cappuccino System, your one touch cappuccino has never been so easy.

## High capacity & compact design



Enjoy more room and go longer without refill thanks to the high-capacity bean, water, and waste containers in a super-compact design. This smart, super-automatic machine provides you with maximum convenience and top notch performance thanks to a large capacity water tank, bean and waste container.

## Thermoblock



The Thermoblock ensures a hot coffee and cappuccino for your family always at the perfect temperature. The secret is in its light aluminum and stainless steel body, which can reach hot temperatures, fast.

## Quick Milk clean



The unique one-touch carafe quick clean allows you to thoroughly rinse the milk system at your convenience after every use

# Specifications

## General specifications

**Milk Solution:** Easy Cappuccino

**User Interface:** LED Buttons

## Technical specifications

**Capacity milk carafe:** 0.5 L

**Capacity waste container:** 15 servings

**Frequency:** 50 Hz

**Max. cup height:** 152 mm

**Voltage:** 230 V

**Color & Finishing:** Silver Paint

**Cord length:** >100 cm

**Filter compatibility:** Brita Intenza

**Waste container:** Frontal access

**Water tank:** Access from the top

**Weight of product:** 7.2 kg

**Product dimensions:** 215 x 330 x 429 mm

**Coffee bean capacity:** 250 g

**Capacity water tank:** 1.8 L

## Customization

**Aroma Strength Settings:** 2

**Grinder Settings:** 5

**Pre Brew Aroma control:** No

**User Profiles:** 1

**Coffee and Milk Length:** Adjustable

## Variety

**Beverages:** Espresso, Hot water, Cappuccino,

Coffee, Milk froth

**Coffee Powder Option:** No

**Double Cup**

**Milk Double Cup:** No

## Other features

**Auto-Rinse & Guided descaling**

**Main Switch ON / OFF button**

**Quick Heat Boiler**

**Removable brew group**

