

# PHILIPS

## Saeco

Super-automatic  
espresso machine

Syntia

Focus

Black



HD8833/13



## Live the pleasure of Italian espresso at home

### Compact and stylish bean-to-cup system

Syntia is the perfect synthesis of compactness, performance, design and high end materials—everything for your Italian espresso enjoyment at a single touch

#### Enjoy an Italian lifestyle at home

- Compact and stylish
- One touch espresso and long coffee

#### Grind your favourite coffee beans

- Play with the coffee's richness with our adjustable grinders

#### Easy to use

- Intuitive colour coded user interface
- Ergonomic in day to day operation

#### Easy to clean and maintain

- Always a clean machine thanks to automatic circuit cleaning
- Easy cleaning thanks to removable brewing group

# Highlights

## Compact and stylish



Compact and stylish, the Syntia coffee machine is designed to delight both your palate and your eyes - the perfect fit for a modern kitchen.

## Espresso and long coffee



Whether you want to enjoy an espresso or a long coffee, your favourites are accessible at the touch of a button

## 5-step adjustable grinders



Different coffee blends require different levels of granularity for the full flavour to unfold. The grind granularity of this espresso machine can

be adjusted in 5 settings, from the finest grind, for a full-bodied espresso, to the coarsest, for a lighter café crème.

## Automatic circuit cleaning



Saeco designed this espresso machine to automatically clean its coffee circuit with water when the machine is started up or switched off. This delivers a great, fresh taste with each cup of coffee.

## Removable brewing group



The brewing group, a Saeco invention, is the heart of our espresso machines, ensuring automation. The brewing group is, depending on the model, easily accessible from the front or side. It can be removed effortlessly for easy cleaning by rinsing under the tap, ensuring maximum hygiene.

## Colour coded user interface



Easy and intuitive interactions thanks to the combination of LED and buttons — this interface directly communicates the key operating messages.

## Ergonomic day to day



Saeco is a synonym for convenience: refilling beans or water, emptying the coffee-dump box or the drip tray, all compartments of the full automatic coffee machine are directly accessible.

# Specifications

## Perfect Espresso

**Espresso technology:** Saeco adapting system, Aroma-system: pre-brewing

## Multi-Beverage

**Milk Variations:** Pannarello: milk frothing

## Easy to use

**Cleaning and maintenance:** Automatic coffee circuit rinse

**Usage:** Adjustable coffee dispenser, Bypass for

grinded coffee, Frontal access to all functions, Rapid steam, Removable brewing group, Removable water tank

## Technical data

**Boiler:** Stainless steel

**Frequency:** 50 Hz

**Power:** 1400 W

**Voltage:** 240 V

**Pump Pressure:** 15 Bar

## Weight and dimensions

**Maximum cup height:** 110 mm

**Product dimensions (L x D x H):** 256 x 315 x 415 mm

**Coffee bean capacity:** 250 gr

**Dump box capacity:** 8 servings

**Water tank capacity:** 1.2 l

