

PHILIPS

Saeco

Super-automatic
espresso machine

Syntia

Syntia

Focus

Black



HD8833/18



Live the pleasure of Italian espresso at home

Compact and stylish bean-to-cup system

Syntia is the perfect synthesis of compactness, performance, design and high end materials—everything for your Italian espresso enjoyment at a single touch

Enjoy an Italian lifestyle at home

- Compact and stylish
- One touch espresso and long coffee

Grind your favourite coffee beans

- Play with the coffee's richness with our adjustable grinders

Easy to use

- Intuitive colour coded user interface
- Ergonomic in day to day operation

Easy to clean and maintain

- Always a clean machine thanks to automatic circuit cleaning
- Easy cleaning thanks to removable brewing group

Highlights

Compact and stylish



Compact and stylish, the Syntia coffee machine is designed to delight both your palate and your eyes - the perfect fit for a modern kitchen.

Espresso and long coffee



Whether you want to enjoy an espresso or a long coffee, your favourites are accessible at the touch of a button

5-step adjustable grinders



Different coffee blends require different levels of granularity for the full flavour to unfold. The grind granularity of this espresso machine can

be adjusted in 5 settings, from the finest grind, for a full-bodied espresso, to the coarsest, for a lighter coffee.

Automatic circuit cleaning




Saeco designed this espresso machine to automatically clean its coffee circuit with water when the machine is started up or switched off. This delivers a great, fresh taste with each cup of coffee.

Removable brewing group



The brewing group, a Saeco invention, is the heart of our espresso machines, ensuring automation. The brewing group is, depending on the model, easily accessible from the front or side. It can be removed effortlessly for easy cleaning by rinsing under the tap, ensuring maximum hygiene.

Colour coded user interface



Easy and intuitive interactions thanks to the combination of LED and buttons — this interface directly communicates the key operating messages.

Ergonomic day to day



Saeco is a synonym for convenience: refilling beans or water, emptying the coffee-dump box or the drip tray, all compartments of the full automatic coffee machine are directly accessible.

Specifications

Technical specifications

Number of water boilers: 1 boiler

Supported coffee types: Ground coffee, Whole coffee beans

Perfect Espresso

Espresso technology: Saeco adapting system, Aroma-system: pre-brewing

Service

2-year worldwide guarantee

Multi-Beverage

Milk Variations: Pannarello: milk frothing

Easy to use

Cleaning and maintenance: Automatic coffee circuit rinse

Usage: Adjustable coffee dispenser, Bypass for grinded coffee, Frontal access to all functions, Rapid steam, Removable brewing group, Removable water tank

Technical data

Boiler: Stainless steel

Frequency: 50 Hz

Power: 1400 W

Voltage: 240 V

Pump Pressure: 15 Bar

Weight and dimensions

Maximum cup height: 110 mm

Product dimensions (L x D x H): 256 x 315 x 415 mm

Coffee bean capacity: 250 gr

Waste container capacity: 8 servings

Water tank capacity: 1.2 l

