

PHILIPS

Saeco

Super-automatic
espresso machine

Syntia

Class

Black



HD8836/12



Live the pleasure of Italian espresso at home

Compact and stylish bean-to-cup system

Syntia is the perfect synthesis of compactness, performance, design and high end materials—everything for your Italian espresso enjoyment at a single touch

Enjoy an Italian lifestyle at home

- Compact and stylish
- One touch espresso and long coffee

Grind your favourite coffee beans

- Play with the coffee's richness with our adjustable grinders
- Adjust coffee length, temperature, strength

Easy to use

- Self-explanatory, colour-coded user interface
- Ergonomic in day to day operation

Easy to clean and maintain

- Always a clean machine thanks to auto-clean and descaling
- Easy cleaning thanks to removable brewing group

Highlights

Compact and stylish



Compact and stylish, the Syntia coffee machine is designed to delight both your palate and your eyes - the perfect fit for a modern kitchen.

Espresso and long coffee



Whether you want to enjoy an espresso or a long coffee, your favourites are accessible at the touch of a button

5-step adjustable grinders



Different coffee blends require different levels of granularity for the full flavour to unfold. The grind granularity of this espresso machine can

be adjusted in 5 settings, from the finest grind, for a full-bodied espresso, to the coarsest, for a lighter café crème.

Auto-cleaning and descaling



Saeco designed this espresso machine to automatically clean its coffee circuit with water when starting up or switching off to deliver a great, fresh taste with each cup of coffee. Regular descaling prolongs your espresso machine's life. This machine will not only prompt when descaling is needed, the automated descaling process will start and guide you with clear on-screen messages when you have to intervene. Descaling has never been so easy!

Removable brewing group



The brewing group, a Saeco invention, is the heart of our espresso machines, ensuring automation. The brewing group is, depending on the model, easily accessible from the front

or side. It can be removed effortlessly for easy cleaning by rinsing under the tap, ensuring maximum hygiene.

Colour coded user interface

Enjoy direct and clear interaction thanks to the self-explanatory icons display. For maximum convenience the icons are coloured according to the traffic light colours: Red requires action, Yellow means the coffee machine is "busy" (e.g. heating up) and Green is ready to use.

Coffee customisation



Saeco machines offer you the possibility of customising your coffee exactly the way you like it - from the most intense espresso to a mild cup of long coffee.

Ergonomic day to day



Saeco is a synonym for convenience: refilling beans or water, emptying the coffee-dump box or the drip tray, all compartments of the full automatic coffee machine are directly accessible.

Specifications

Perfect Espresso

Espresso technology: Saeco adapting system, Aroma-system: pre-brewing

Multi-Beverage

Milk Variations: Pannarello: milk frothing

Easy to use

Cleaning and maintenance: Automatic coffee circuit rinse

Usage: Adjustable coffee dispenser, Bypass for

grinded coffee, Frontal access to all functions, Rapid steam, Removable brewing group, Removable water tank

Technical data

Boiler: Stainless steel
Frequency: 50 Hz
Power: 1400 W
Voltage: 230 V
Pump Pressure: 15 Bar

Weight and dimensions

Maximum cup height: 110 mm
Product dimensions (L x D x H): 256 x 315 x 415 mm
Coffee bean capacity: 250 gr
Dump box capacity: 8 servings
Water tank capacity: 1.2 l

