

# PHILIPS

## Saeco

Super-automatic  
espresso machine

Syntia

Classic Milk Frother

Stainless steel



HD8837/47



## Live the pleasure of Italian espresso at home compact and stylish bean-to-cup system

the perfect synthesis between compactness, performance, design and premium materials

### Authentic Italian coffee perfection

- Delicious milk froth thanks to the classic milk frother
- Coffee without waiting thanks to the quick heat boiler
- Coffee without burnt taste thanks to 100% ceramic grinders

### Set the beverages to suit your taste

- Save your favorite coffee settings
- Play with the coffee's richness with our adjustable grinders
- Avoid heat loss and fit every cup with our adjustable spout

### Ease of cleaning and maintaining

- Always a clean machine thanks to auto-clean and descaling
- Easy cleaning thanks to removable brewing group
- Easy cleaning thanks to dishwasher-safe parts
- Cutting-edge design with stainless steel finish

# Highlights

## Stainless steel



The cutting-edge design of your Saeco espresso machine is rounded off by the stainless steel finish. The stainless steel provides a high quality look and will be a highlight on your kitchen counter tops. It also gives greater resistance for a long-lasting performance.

## 100% ceramic grinders



This espresso machine is equipped 100% ceramic grinders. Saeco uses ceramic grinders because of their consistent grind without overheating the coffee bean for an impeccable espresso. Ceramic also ensures long-lasting performance and a totally silent operation.

## Quick heat boiler



The Saeco quick heat boiler technology ensures your machine is always ready. Now you won't have to wait between brewing each espresso, but can prepare coffee after coffee.

## Classic milk frother



This Saeco espresso machine comes with the classic milk frother that baristas call a "Pannarello". It dispenses steam and is immersed in milk to prepare gorgeous milk foam. Unleash your inner barista by preparing your delicious milk specialties the traditional way!

## Saves your coffee settings



You will always get a perfect cup of espresso brewed just for you, according to your personal preference, thanks to our innovative memo function to adjust the coffee length, strength and temperature. Enjoy a superb coffee drink in your favorite cup with just the press of a button.

## Adjustable spout



The adjustable spout on our espresso machines will fit every cup and thus prevents the coffee splashing or cooling down while pouring in your cup. This way your espresso is always served at the right temperature while maintaining a clean machine.

## Dishwasher-safe parts




For your convenience, you can put the Saeco's drip tray and milk frother or milk carafe in the dishwasher. This will save time and ensure a hygienic cleaning.

## 5 step adjustable grinders



Different coffee blends require different levels of granularity for the full flavor to unfold. The grind granularity of this espresso machine can be adjusted in 5 settings, from the finest grind, for a full bodied espresso, to the coarsest, for a lighter coffee.

## Removable brewing group



The brewing group, a Saeco invention, is the heart of our espresso machines, ensuring automation. The brewing group is, depending on the model, easily accessible from the front or side. It can be removed effortlessly for easily cleaning by rinsing under the tap ensuring maximum hygiene.

# Specifications

## Technical specifications

**Supported coffee types:** Ground coffee, Whole coffee beans

**Water pressure in pump:** 15 bar (perfect espresso)

**Removable brewing group**

**Country of origin:** Designed in Italy, Made in Italy

**Cord length:** 80 cm

**Number of water boilers:** 1 boiler

**Frequency:** 60 Hz

**Power:** 1400 W

**Voltage:** 120 V

**Boiler material:** Stainless steel (Inox)

## Perfect Espresso

**Espresso technology:** Saeco adapting system, Aroma-system: pre-brewing

## Service

1-year guarantee

## Multi-Beverage

**Milk Variations:** Pannarello: milk frothing

## Easy to use

**Cleaning and maintenance:** Automatic coffee circuit rinse

**Usage:** Adjustable coffee dispenser, Bypass for

grinded coffee, Frontal access to all function, Rapid steam, Removable brewing group, Removable watertank

## Weight and dimensions

**Product weight:** 8.9 kg

**Maximum cup height:** 110 mm

**Product dimensions (L x D x H):** 256 x 315 x 415 mm

**Coffee bean capacity:** 250 gr

**Waste container capacity:** 8 servings

**Water tank capacity:** 1.2 L

## Design

**Colour:** Stainless steel

**Materials and finishing:** Stainless steel

