

PHILIPS

Saeco

Super-automatic
espresso machine

Syntia

Cappuccino



HD8838/02



SYNTIA

Jug lid for the jug of the SENSEO® SARISTA Compact and stylish bean-to-cup system

Syntia Cappuccino is the perfect synthesis of compactness, performance, design and high end materials - everything for your Italian espresso and cappuccino enjoyment at a single touch

Enjoy Italian lifestyle at home

- Compact and stylish
- One touch espresso, long coffee and cappuccino

Grind your favorite coffee beans

- Play with the coffee's richness with our adjustable grinders
- Adjust coffee length, temperature, strength

Easy to use

- Self explanatory color coded user interface
- Ergonomic in day-by-day operations
- Integrated automatic milk function

Ease of cleaning and maintaining

- Always a clean machine thanks to auto-clean and descaling
- Easy cleaning thanks to removable brewing group

Highlights

Compact and stylish



Compact and stylish the Syntia coffee machine is designed to delight both your palate and your eyes - the perfect fit for a modern kitchen.

Espresso and cappuccino



Whether you want to enjoy an espresso, a cappuccino or a long coffee - your specialties are accessible with the touch of a button

5 step adjustable grinders



Different coffee blends require different levels of granularity for the full flavor to unfold. The grind granularity of this espresso machine can be adjusted in 5 settings, from the finest grind, for a full bodied espresso, to the coarsest, for a lighter coffee.

Auto cleaning and descaling



Saeco designed this espresso machine to automatically clean its coffee circuit with water upon starting up or switching off of the machine, this delivers a great, fresh taste with each cup of coffee. Regular descaling prolongs your espresso machine's life. This machine will not only prompt when descaling is needed, the automated descaling process will start on your machine and guides you with clear on-screen messages when you have to intervene. Descaling has never been so easy!

Removable brewing group



The brewing group, a Saeco invention, is the heart of our espresso machines, ensuring automation. The brewing group is, depending on the model, easily accessible from the front or side. It can be removed effortlessly for easily cleaning by rinsing under the tap ensuring maximum hygiene.

Color coded user interface

Enjoy direct and clear interaction thanks to the self-explanatory icons display. For maximum convenience the icons are colored according to the traffic light colors: Red requires action, Yellow means the coffee machine is "busy" (like heating up). Green is ready to use.

Coffee customization



Saeco machines offer you the possibility to customize the coffee exactly the way you like it - from the most intense espresso to a mild cup of long coffee.

Ergonomic day-by-day



Saeco is a synonym for convenience: refilling beans or water, emptying the coffee-dump box or the drip tray, all compartments of the full automatic coffee machine are directly accessible.

Automatic milk function



With the integrated milk frother, all you have to do is filling it with milk and simply pressing the cappuccino button. Your drink will be served within seconds as creamy froth milk will be poured automatically into your beverage.

Specifications

Perfect Espresso

Espresso technology: Saeco adapting system, Aroma-system: pre-brewing

Multi-Beverage

Milk Variations: Integrated auto milk function

Easy to use

Cleaning and maintenance: Automatic coffee circuit rinse

Usage: Adjustable coffee dispenser, Bypass for

grinded coffee, Frontal access to all function, Rapid steam, Removable brewing group, Removable watertank

Technical data

Boiler: Stainless steel

Frequency: 50 Hz

Power: 1400 W

Voltage: 230 V

Pump Pressure: 15 bar

Weight and dimensions

Product dimensions (L x D x H): 330x450x415 mm

Coffee bean capacity: 250 gr

Dump box capacity: 8 servings

Water tank capacity: 1.2 l

