



Saeco Energica  
Super-automatic  
espresso machine

- Integrated milk jug & frother
- Stainless steel



HD8852/47



# Perfect, hot, clean.

That's the premium milk froth experience

Only Saeco Energica espresso machine delivers the perfect espresso and milk experience, always ready, equipped with integrated Milk Frother.

### Authentic Italian coffee perfection

- Perfect milk froth thanks to the integrated milk carafe
- Milk specialties without the wait thanks to a double boiler
- Coffee without burnt taste thanks to 100% ceramic grinders

### Set the beverages to suit your taste

- Save your favorite coffee settings
- Play with the coffee's richness with our adjustable grinders
- Boost coffee crema and body


### Ease of cleaning and maintaining

- Always a clean machine thanks to auto-clean and descaling
- Hygienic milk frothing thanks to automated dual cleaning
- Easy cleaning thanks to removable brewing group
- Cutting-edge design with stainless steel finish

**PHILIPS**

Saeco, a Philips brand

 **Saeco**



# Highlights

## Stainless steel



The cutting-edge design of your Saeco espresso machine is rounded off by the stainless steel finish. The stainless steel provides a high quality look and will be a highlight on your kitchen counter tops. It also gives greater resistance for a long-lasting performance.

## 100% ceramic grinders



This espresso machine is equipped 100% ceramic grinders. Saeco uses ceramic grinders because of their consistent grind without overheating the coffee bean for an impeccable espresso. Ceramic also ensures long-lasting performance and a totally silent operation.

## 8 step adjustable grinders



Different coffee blends require different levels of granularity for the full flavor to unfold. The grind granularity of this espresso machine can be adjusted in 8 settings, from the finest grind, for a full bodied espresso, to the coarsest, for a lighter coffee.

## Saves your coffee settings



You will always get a perfect cup of espresso brewed just for you, according to your personal preference, thanks to our innovative memo function to adjust the coffee length, strength and temperature. Enjoy a superb coffee drink in your favorite cup with just the press of a button.

## Removable brewing group



The brewing group, a Saeco invention, is the heart of our espresso machines, ensuring automation. The brewing group is, depending on the model, easily accessible from the front or side. It can be removed effortlessly for easily cleaning by rinsing under the tap ensuring maximum hygiene.

## Automatic dual cleaning carafe



This Saeco espresso machine comes with a fully automated dual clean function for its milk carafe. The dual cleaning uses two independent steam cycles to swiftly rinse your milk carafe after each coffee drink you prepare, for a fresh milk drink everytime. Hygienic milk frothing was never this easy.

# Specifications

## Perfect Espresso

- Espresso technology: Saeco adapting system, Aroma-system: pre-brewing

## Service

- 1-year guarantee

## Technical specifications

- Supported coffee types: Ground coffee, Whole coffee beans
- Water pressure in pump: 15 bar (perfect espresso)
- Removable brewing group
- Country of origin: Designed in Italy, Made in Italy
- Cord length: 80 cm
- Number of water boilers: 1 boiler
- Frequency: 60 Hz
- Power: 1400 W
- Voltage: 120 V
- Boiler material: Stainless steel (Inox)

## Multi-Beverage

- Milk Variations: Integrated auto milk function, Milk quantity selector, Removable milk carafe

## Easy to use

- Cleaning and maintenance: Automatic coffee circuit rinse, Automatic milk circuit rinse, Descaling cycle
- Usage: Adjustable coffee dispenser, Bypass for grinded coffee, Frontal access to all function, Instant steam (2 boilers), Removable brewing group, Removable watertank

## Weight and dimensions

- Product weight: 13.4 kg
- Product dimensions (L x D x H): 245 x 360 x 420 mm
- Coffee bean capacity: 300 gr
- Waste container capacity: 11 servings
- Milk carafe capacity: 0.5 L
- Water tank capacity: 1.5 L
- Maximum cup height: 150 mm

## Design

- Colour: Stainless steel
- Materials and finishing: Stainless steel / ABS Plastic