

# PHILIPS

## Saeco

Super-automatic  
espresso machine

Exprelia

Class

Black

5 step adjustable grinder



HD8854/16



## Espresso and cappuccino at a single touch

### With full bean-to-cup customization

The Exprelia is always ready to serve your favorite coffee specialty. What ever you'd like, it's done with a touch of a button, thanks to immediate beverage selection interface - and instantly prepared thanks to the machine's double boiler.

#### **Ease of cleaning and maintaining**

- Always a clean machine thanks to auto-clean and descaling
- Frontal access to removable brewing group
- Immediate beverage selection

#### **Authentic Italian coffee perfection**

- Double boiler for fast and professional results
- Integrated automatic milk function with Easy Refill
- Coffee without burnt taste thanks to 100% ceramic grinders

#### **Set the beverages to suit your taste**

- Save your favorite coffee settings
- Play with the coffee's richness with our adjustable grinders
- SBS: crema & body boost

# Highlights

## Immediate beverage selection



Whether you want a cappuccino or an espresso, with the immediate beverage selection you can enjoy your personally customized beverage specialty at the touch of a button

## Auto cleaning and descaling



Saeco designed this espresso machine to automatically clean its coffee circuit with water upon starting up or switching off of the machine, this delivers a great, fresh taste with each cup of coffee. Regular descaling prolongs your espresso machine's life. This machine will not only prompt when descaling is needed, the automated descaling process will start on your machine and guides you with clear on-screen messages when you have to intervene. Descaling has never been so easy!

## Removable brewing group



The brewing group is at the heart of every fully automatic coffee machine and it should always be kept clean. A task that doesn't get any more convenient than with a Saeco: remove, rinse and re-insert – finished.

## Double boiler for fast results



Dual and independent heating systems enable you to make as many Latte Macchiato and Cappuccino as you need, without any loss of performance.

## Integrated automatic milk

Enjoy your milk specialties without any stop: it is possible to refill the carafe with milk even while the integrated milk frother is plugged in and working.

## Saves your coffee settings



You will always get a perfect cup of espresso brewed just for you, according to your personal preference, thanks to our innovative memo

function to adjust the coffee length, strength and temperature. Enjoy a superb coffee drink in your favorite cup with just the press of a button.

## 100% ceramic grinders



This espresso machine is equipped 100% ceramic grinders. Saeco uses ceramic grinders because of their consistent grind without overheating the coffee bean for an impeccable espresso. Ceramic also ensures long-lasting performance and a totally silent operation.

## 8 step adjustable grinders



Different coffee blends require different levels of granularity for the full flavor to unfold. The grind granularity of this espresso machine can be adjusted in 8 settings, from the finest grind, for a full bodied espresso, to the coarsest, for a lighter coffee.

## SBS: crema & body boost



Only with Saeco you can adjust the counter pressure to get your preferred quantity of crema in your espresso.

# Specifications

## Technical specifications

**Boiler material:** Stainless steel (Inox)

**Number of water boilers:** 1 boiler

**Water pressure in pump:** 15 bar (perfect espresso)

**Supported coffee types:** Ground coffee, Whole coffee beans

**Country of origin:** Made in Italy, Designed in Italy

**Removable brewing group**

**Power:** 1500 W

**Voltage:** 120 V

**Frequency:** 60 Hz

**Cord length:** 80 cm

## Sustainability

**Automatic Stand-by Option**

## Service

**2-year worldwide guarantee**

## Perfect Espresso

**Espresso technology:** Saeco adapting system, Aroma-system: pre-brewing, SBS: creme adaptor

## Multi-Beverage

**Milk Variations:** Integrated auto milk function, Milk quantity selector, Removable milk carafe

## Easy to use

**Cleaning and maintenance:** Automatic coffee circuit rinse, Automatic milk circuit rinse, Descaling cycle

**Usage:** Adjustable coffee dispenser, Bypass for

grinded coffee, Frontal access to all function, Instant steam (2 boilers), Removable brewing group, Removable watertank

## Weight and dimensions

**Coffee bean capacity:** 300 gr

**Maximum cup height:** 150 mm

**Product weight:** 13.4 kg

**Waste container capacity:** 11 servings

**Milk carafe capacity:** 0.5 L

**Water tank capacity:** 1.5 L

**Product dimensions (L x D x H):** 245 x 360 x 420 mm

