

PHILIPS

Saeco

Super-automatic
espresso machine

Exprelia

Class

Black

5-step adjustable grinder



HD8854/16



Espresso and cappuccino at a single touch

With full bean-to-cup customisation

The Exprelia is always ready to serve your favourite coffee speciality. Thanks to the immediate beverage selection interface, whatever you choose is made at the touch of a button — and instantly prepared thanks to the machine's double boiler.

Easy to clean and maintain

- Always a clean machine thanks to auto-clean and descaling
- Frontal access to removable brewing group
- Immediate beverage selection

Authentic Italian coffee perfection

- Double boiler for fast and professional results
- Integrated automatic milk function with Easy Refill
- Coffee without burnt taste thanks to 100% ceramic grinders

Set the beverages to suit your taste

- Save your favourite coffee settings
- Play with the coffee's richness with our adjustable grinders
- SBS: crema and body boost

Highlights

Immediate beverage selection



Whether you want a cappuccino or an espresso, with the immediate beverage selection you can enjoy your personally customised beverage speciality at the touch of a button

Auto-cleaning and descaling



Saeco designed this espresso machine to automatically clean its coffee circuit with water when starting up or switching off to deliver a great, fresh taste with each cup of coffee. Regular descaling prolongs your espresso machine's life. This machine will not only prompt when descaling is needed, the automated descaling process will start and guide you with clear on-screen messages when you have to intervene. Descaling has never been so easy!

Removable brewing group



The brewing group is at the heart of every fully automatic coffee machine and it should always be kept clean. A task that doesn't get any more convenient than with a Saeco: remove, rinse and re-insert — finished.

Double boiler for fast results



Dual and independent heating systems enable you to make as many Latte Macchiatos and Cappuccinos as you need, without any loss of performance.

Integrated automatic milk

Enjoy your milk specialities non-stop: it is possible to refill the carafe with milk even while the integrated milk frother is plugged in and working.

Saves your coffee settings



You will always get a perfect cup of espresso brewed just for you, according to your personal preference, thanks to our innovative memo function for adjusting the coffee length,

strength and temperature. Enjoy a superb coffee drink in your favourite cup at the touch of a button.

100% ceramic grinders



This espresso machine is equipped with 100% ceramic grinders. Saeco uses ceramic grinders because of their consistent grind without overheating the coffee bean, for an impeccable espresso. Ceramic also ensures long-lasting performance and totally silent operation.

8-step adjustable grinders



Different coffee blends require different levels of granularity for the full flavour to unfold. The grind granularity of this espresso machine can be adjusted in 8 settings, from the finest grind, for a full-bodied espresso, to the coarsest, for a lighter coffee.

SBS: crema and body boost



Only with Saeco can you adjust the counter pressure to get your preferred quantity of crema in your espresso.

Specifications

Technical specifications

Boiler material: Stainless steel (Inox)

Number of water boilers: 1 boiler

Water pressure in pump: 15 bar (perfect espresso)

Supported coffee types: Ground coffee, Whole coffee beans

Country of origin: Made in Italy, Designed in Italy

Removable brewing group

Power: 1500 W

Voltage: 120 V

Frequency: 60 Hz

Cord length: 80 cm

Sustainability

Automatic Standby Option

Service

2-year worldwide guarantee

Perfect Espresso

Espresso technology: Saeco adapting system, Aroma-system: pre-brewing, SBS: creme adaptor

Multi-Beverage

Milk Variations: Integrated auto milk function, Milk quantity selector, Removable milk carafe

Easy to use

Cleaning and maintenance: Automatic coffee circuit rinse, Automatic milk circuit rinse, Descaling cycle

Usage: Adjustable coffee dispenser, Bypass for

grinded coffee, Frontal access to all functions, Instant steam (2 boilers), Removable brewing group, Removable water tank

Weight and dimensions

Coffee bean capacity: 300 gr

Maximum cup height: 150 mm

Product weight: 13.4 kg

Waste container capacity: 11 servings

Milk carafe capacity: 0.5 l

Water tank capacity: 1.5 l

Product dimensions (L x D x H): 245 x 360 x 420 mm

