

# PHILIPS

## Saeco

Automatic espresso machine

Exprelia

Integrated Milk Carafe

Stainless steel

HD8856/01



## Perfect, hot, clean.

That's the premium milk experience

The Saeco Exprelia coffee machine is always ready to serve your favourite coffee. Whatever you'd like, it's done at the touch of a button, thanks to the immediate beverage selection interface and the coffee machine's double boiler.

### Authentic Italian coffee perfection

- Integrated automatic milk function with Autoclean
- Double boiler for instant steam
- No more burnt coffee thanks to our 100% ceramic grinders

### Set the beverages to suit your taste

- Memo function thanks to an intuitive display interface
- Adjustable grinder granularity
- SBS: patented adjustable espresso crema and body structure

### Easy to clean and maintain

- Always a clean machine thanks to auto-clean and descaling
- Fully automated dual cleaning milk carafe
- One-click removable brewing group
- Sleeker look and design thanks to stainless steel finishes

# Highlights

## Sleeker look and design



Cutting-edge design and longer-lasting performance are the result of the appliance's stainless steel finishes.

## 100% Ceramic Grinders



Our ceramic grinders never overheat, ensuring perfect grinding, long-lasting performance and totally silent operation

## Adjustable grinder granularity



8 grinder settings from the finest to a very rough grind.

## Memo function



You will always get a perfect cup brewed just for you, according to your personal preference, thanks to our Memo function with adjustable

length, strength and temperature. Pressing a button is all you'll need to do to enjoy a superb beverage in your favourite cup.

## One-click removable group



The brewing group – a Saeco invention – is the heart of our machines, ensuring that the machine makes everything on its own. Thanks to its easy access, you can effortlessly remove it for regular cleaning with just one click.

## Fully automated dual cleaning



Two independent steam cycles ensure a fully automated deep clean after every beverage.

## Auto-cleaning and descaling



Saeco designed this espresso machine to automatically clean its coffee circuit with water when starting up or switching off to deliver a great, fresh taste with each cup of coffee. Regular descaling prolongs your espresso machine's life. This machine will not only prompt when descaling is needed, the automated descaling process will start and

guide you with clear on-screen messages when you have to intervene. Descale has never been so easy!

## Double boiler



Optimal conditions for everything: two independent circuits ensure quick and convenient coffee preparation straight after frothing the milk.

## Integrated milk function



Integrated automatic milk function with Autoclean

## SBS (Saeco Brewing System)



Saeco exclusively allows you to adjust your espresso's intensity, altering the crema and body structure as it is dispensed. By simply turning the knob, you can prepare the crema exactly according to your taste. A little knob that makes a big difference.

# Specifications

## Perfect Espresso

**Espresso technology:** Saeco adapting system, Aroma-system: pre-brewing, SBS: creme adaptor

## Multi-Beverage

**Milk Variations:** Integrated auto milk function, Milk quantity selector, Removable milk carafe

## Easy to use

**Cleaning and maintenance:** Automatic coffee circuit rinse, Automatic milk circuit rinse, Descaling cycle

**Usage:** Adjustable coffee dispenser, Bypass for

grinded coffee, Frontal access to all functions, Instant steam (2 boilers), Removable brewing group, Removable water tank

## Energy saving

**Energy saving:** Selectable Eco-mode

## Technical data

**Boiler:** Stainless steel

**Frequency:** 50 Hz

**Power:** 1400 W

**Voltage:** 230 V

**Pump Pressure:** 15 Bar

## Weight and dimensions

**Product dimensions (L x D x H):** 245 x 420 x 360 mm

**Weight:** 14.2 kg

**Coffee bean capacity:** 300 gr

**Dump box capacity:** 11 servings

**Milk carafe capacity:** 0.5 l

**Water tank capacity:** 1.6 l

