



**Saeco Intelia Deluxe
Super-automatic
espresso machine**

- 6 Beverages
- Integrated milk carafe
- Stainless Steel
- AquaClean



HD8906/01

The quality you demand, the ease of use you expect

A timeless design Made in Italy

Saeco presents Intelia Deluxe. A smartly crafted piece of technology delivering proven quality, convenience, and divine coffee. Housed in a stainless steel body with a timeless design, Intelia is an ambassador of Italian craftsmanship.

Any coffee for any moment

- Enjoy 6 beverages at your fingertips
- One-touch Cappuccino with the integrated milk carafe
- Adjust the length, 5 aroma strength and 10 grinder settings
- Adjust and store your personal user profile

Every coffee crafted to perfection

- 20,000 cups of finest coffee with durable ceramic grinders
- Perfect milk foam thanks to Latte Perfetto technology
- Iconic stainless steel finishing, shaped to precision
- Hot coffee from the first cup with Thermoblock

Attentive and anticipating at your command

- Featuring AquaClean for up to 5000* cups without descaling
- Clean milk residues after every use with milk clean function
- Smartly designed to fit any kitchen countertop
- Enjoy a great coffee with Auto-Rinse & guided descaling



PHILIPS

Saeco, a Philips brand



Highlights

100% ceramic grinders



Our grinders are made of high-tech ceramic: exceptionally hard and precise. Fresh beans are gently ground, without risk of overheating: extracting all the best flavors and aroma, delivering a superior coffee taste for at least 20,000 cups.

6 beverages



Enjoy a wide variety of drinks to suit any occasion. Whether you crave for an espresso, a coffee or a milk based recipe, your Super-automatic machine delivers a perfect in-cup result with no hassle and in no time!

AquaClean filter



AquaClean

AquaClean is our patented water filter, designed to improve the quality of your coffee

by purifying water. It also prevents scale build-up in the water circuit of your coffee machine: make up to 5000* cups without descaling by replacing the filter regularly.

Auto-Rinse & Guided descaling




This espresso machine automatically cleans its coffee circuit with water upon starting up or switching off of the machine, this delivers a great, fresh taste with each cup of coffee. Regular descaling prolongs your espresso machine's life. This machine will prompt when descaling is needed. It will guide you with on-screen messages what you have to do and when.

Customize your coffees



This Super-Automatic machine offers an abundance of indulgent options to customize your beverage to your taste. You can easily personalize and memorize length, strength and temperature for each drink. Feel free to explore, experiment and dream up any drink!

Front loading for easy access



Your super-automatic espresso machine is effortless to use thanks to the frontal loading of the water tank and the dump box.

Integrated milk carafe



Enjoy super creamy cappuccino at the perfect temperature, in the easiest way possible. Simply pour milk into the carafe, plug it into the machine, and select your preferred beverage. Whether it's a cappuccino or frothed milk, your drink will be served within seconds, with a splash-free flow at the ideal temperature.

Specifications

General specifications

- Milk Solution: Integrated Milk Carafe, Quick Milk clean
- User Interface: Basic Display

Technical specifications

- Capacity milk carafe: 0.5 L
- Capacity waste container: 10 servings
- Capacity water tank: 1.5 L
- Frequency: 50 Hz
- Max. cup height: 115 mm
- Voltage: 230 V
- Coffee bean capacity: 300 g
- Color & Finishing: Stainless Steel
- Cord length: >100 cm
- Filter compatibility: AquaClean
- Product dimensions: 256 x 340 x 444 mm
- Waste container: Frontal access
- Water tank: Frontal access
- Weight of product: 8.9 kg
- Country of origin: Italy

Customization

- Aroma Strength Settings: 5
- Coffee and Milk Length: Adjustable
- Grinder Settings: 10
- Pre Brew Aroma control
- Temperature settings: 3
- User Profiles: 1

Other features

- Auto-Rinse & Guided descaling
- Gusto perfetto
- Main Switch ON / OFF button: No
- Quick Heat Boiler
- Removable brew group

Variety

- Beverages: Baby Cappuccino, Cappuccino, Espresso, Espresso Lungo, Hot water, Milk froth
- Coffee Powder Option
- Double Cup
- Milk Double Cup: No