



**Saeco Incanto  
Super-automatic  
espresso machine**

- 4 Beverages
- Classic Milk Frother
- Black
- 5 step adjustable grinder



**HD8911/47**

## Elegant design. Impressive coffee quality.

### Advanced technology delivering maximum flavor

The Saeco Incanto has set a new standard in its class. The strikingly refined casing houses high-quality Italian technology, engineered to brew divine coffee, every time. Your coffee dreams have finally been answered.

#### **Advanced technology designed for coffee perfection**

- 20,000 cups of finest coffee with durable ceramic grinders
- Enjoy hot coffee in no time with the Quick Heat Boiler
- Velvety milk foam with the Classic Milk Frother
- Fine-tune the coffee's richness with 5 grinder settings

#### **High comfort is part of the experience**

- Designed for efficiency
- Auto-cleaning cycle removes any hassle
- The fully removable brewing group can be cleaned in no time

#### **A variety of coffees customized to your taste**

- Decaffeinated with equal zest with the Powder Option
- The strength selection remembers just how strong you like it

 **Saeco**

**PHILIPS**

Saeco, a Philips brand



# Highlights

## 100% Ceramic grinders



Our grinders are made of high-tech ceramic: exceptionally hard and precise. Fresh beans are gently ground, without risk of overheating: extracting all the best flavors and aroma, delivering a superior coffee taste for at least 20,000 cups.

## Quick Heat Boiler



When time is of the essence, you can brew perfect espresso and cappuccino without the wait, thanks to the Quick Heat Boiler. The secret is in its light aluminum and stainless steel body, which can reach hot temperatures, fast.

## Classic Milk Frother



The Classic Milk Frother is for those who love to assume the role of master craftsman, and it's just easy. Within seconds you can create a rich, silky layer of foam - the crowning glory of your coffee.

## Powder Option



Sometimes it's nice to have the option of a full-bodied, delicious coffee, without the caffeine kick. Thanks to the Powder Option you can make decaffeinated coffee whenever you please.

## Designed for efficiency



Saeco Incanto ingeniously combines efficiency with attentiveness to meet the highest

standards for your home – keeping water consumption and energy usage low. And with the programmable stand-by, just tell the Saeco Incanto when it won't be needed and it will switch itself off automatically. Easy.

## Auto-cleaning



The automatic cleaning cycle makes it easy to look after, and it increases the machine's longevity – giving you more time to enjoy your coffee instead of cleaning up.

## Removable brewing group



Efficiency and ease of use were key inspirations when Saeco invented the first brewing group 30 years ago. And to this day, it still proves to be an inspired, resolute piece of technology. As always, it's so simple to clean – just remove it and wash it under the tap for a few seconds, then re-insert it just as easily.

# Specifications

## Accessories

- Included: Water filter

## Design

- Color: Black

## Finishing

- Material boiler: Stainless steel (Inox)
- Material drip tray: Stainless steel
- Material of main body: Plastic
- Material panarello: Stainless steel
- Material water tank: Plastic

## Country of origin

- Made in: Europe

## General specifications

- Coffee strength settings: 5
- Suitable for: Whole coffee beans, ground coffee powder
- Cups at the same time: 2
- Customizing per drink: Adjustable coffee strength, Adjustable cup volume, Adjustable temperature
- Ease of cleaning & maintenance: Automatic descaling cycle, Automatic rinse cycle, Removable brewing group
- Ease of use and comfort: Adjustable spout, Automatic stand-by, Display, Removable drip-tray, Removable water tank, Automatic shut-off
- Grinder settings: 5
- Special functions: Ceramic grinder, Hot water

- option, Manual milk frother Pannarello, Ground coffee option, Steam option
- Temperature settings: 3
- Type of display: LCD
- Coffee drinks: Espresso, Espresso Lungo, Milk Froth, Hot Water

## Sustainability

- Power consumption brewing: 1850 W

## Technical specifications

- Brewing time one cup: 45 (espresso) to 100 (long coffee) sec
- Capacity bean container: 250 gr
- Capacity waste container: 15 servings
- Capacity water tank: 1.8 L
- Cord length: 0.8 m
- Frequency: 50 Hz
- Max. cup height: 152 mm
- Pump pressure: 15 bar
- Voltage: 230 V
- Water boilers: 1

## Weight and dimensions

- Dimensions of product (WxDxH): 215 x 429 x 330 mm
- Weight of product: 7.2 kg

## Service

- 1-year guarantee