



Saeco PicoBaristo  
Super-automatic  
espresso machine

- 11 Beverages
- Integrated premium milk carafe
- Black
- 10-step adjustable grinder

HD8927/37



## The largest variety from a compact machine

Enjoy 5000 cups of divine coffee without descaling

PicoBaristo is a premium compact machine which spoils coffee lovers for variety. Via the user interface you can choose from a wide choice of specialties at one touch. And with the AquaClean filter you can enjoy 5,000 cups\* without descaling

### Advanced technology designed for coffee perfection

- Delicious hot Cappuccino and Latte Macchiato at one touch
- 20,000 cups of finest coffee with durable ceramic grinders
- Enjoy hot coffee in no time with the Quick Heat Boiler

### A variety of coffees customized to your taste

- Many specialty coffees from espresso to Latte Macchiato
- The strength selection remembers just how strong you like it
- Fine-tune the coffee's richness with 10 grinder settings

### High comfort is part of the experience

- Up to 5000 cups\* without descaling with AquaClean filter
- Clean milk carafe after every use with quick clean function
- Iconic stainless steel front, shaped to precision
- Tactile backlit display and seamless navigation

**PHILIPS**

Saeco, a Philips brand

 **Saeco**



# Highlights

## AquaClean filter



## AquaClean

Saeco's new and patented innovation, AquaClean water filter, ensures you make the most out of your full automatic coffee machine. By changing the filter at machine request, you will not need to descale your machine for up to 5000 cups\*, while getting the benefit of clear and purified water. As an added benefit, the descaling notification alarm is automatically deactivated once AquaClean is installed in your favourite Saeco coffee machine.

## Quick Heat Boiler



When time is of the essence, you can brew perfect espresso and cappuccino without the wait, thanks to the Quick Heat Boiler. The secret is in its light aluminum and stainless steel body, which can reach hot temperatures, fast.

## Customize your coffee



Choose your ideal strength from the 5 different settings, select the length and the temperature. You can easily save your desired coffee length with the Memo Function for each drink. Then every cup in the future will be customised exactly to your taste. You'll never have to remind it again, unlike the local barista.

## 100% Ceramic grinders



Our grinders are made of high-tech ceramic: exceptionally hard and precise. Fresh beans are gently ground, without risk of overheating: extracting all the best flavors and aroma, delivering a superior coffee taste for at least 20,000 cups.

## 10-settings adjustable grinder



When it comes to the fineness of the grind, this machine never fails to satisfy. Different coffee blends require different levels of granularity for the full flavour to unfold. So the grind granularity of this machine has ten adjustable settings – from the finest grind for a full-bodied espresso, to the coarsest for a lighter coffee.

## One-touch Cappuccino and Latte



Every coffee you prepare will be topped with a silky, milk layer that beckons the taste buds. The milk carafe froths the milk twice, then pours a splash free creamy layer into your cup at just the right temperature. The carafe can also be stored conveniently in the fridge and it is incredibly hygienic.

# Specifications

## Accessories

- Included: Measuring scoop, Water hardness test strip, Cleaning brush, Water filter

## Design

- Color: Black

## Finishing

- Material boiler: Stainless steel (Inox)
- Material drip tray: Stainless steel
- Material water tank: Plastic

## Country of origin

- Made in: Europe

## General specifications

- Coffee strength settings: 5
- Cups at the same time: 2
- Customizing per drink: Adjustable coffee strength, Adjustable cup volume, Adjustable temperature, Memo function cup volume
- Ease of cleaning & maintenance: Automatic descaling cycle, Automatic rinse cycle, Descale indicator, Automatic carafe cleaning, Dishwasher-safe parts, Removable brewing group, AquaClean filter compatible
- Ease of use and comfort: Adjustable spout, Display, Removable drip-tray, Removable water tank, Automatic shut-off
- Grinder settings: 10
- One touch variety: 11
- Special functions: Ceramic grinder, Hot water

option, Integrated carafe, Ground coffee option, Pre-brewing

- Temperature settings: 3
- Type of carafe: Premium carafe
- Type of display: LCD
- Milk Solution: Integrated Milk Carafe

## Sustainability

- Energy label: A-class
- Power consumption brewing: 1850 W

## Technical specifications

- Brewing time one cup: 45 (espresso) to 100 (long coffee) sec
- Capacity bean container: 250 gr
- Capacity milk carafe: 0.5 L
- Capacity waste container: 15 servings
- Capacity water tank: 1.8 L
- Cord length: 1.2 m
- Frequency: 50 Hz
- Max. cup height: 78 - 164 mm
- Pump pressure: 15 bar
- Voltage: 230 V
- Water boilers: 1

## Weight and dimensions

- Dimensions of product (WxDxH): 215 x 429 x 330 mm
- Weight of product: 7.2 kg

## Service

- 1-year guarantee