

# PHILIPS

## Saeco

Super-automatic  
espresso machine

Royal

Brews 7 coffee varieties

Automatic Milk Frother

Silver

5 step adjustable grinder

HD8930/01



## Solid performance, cup after cup

With large capacity containers

The new Saeco Royal espresso machine is the rejuvenation of a trusted classic. What remains unchanged is the extremely solid performance and the generous tanks for beans, water and coffee grounds.

### High comfort is part of the experience

- The fully removable brewing group can be cleaned in no time

### A variety of coffees customized to your taste

- The strength selection remembers just how strong you like it

### Advanced technology designed for coffee perfection

- Velvety froth at one touch with the Automatic Milk Frother

# Highlights

## Removable brewing group



Efficiency and ease of use were key inspirations when Saeco invented the first brewing group 30 years ago. And to this day, it still proves to be an inspired, resolute piece of technology. As always, it's so simple to clean – just remove it and wash it under the tap for a few seconds, then re-insert it just as easily.

## Memo Function



Once you've chosen your ideal strength from the 5 different settings, you can easily save it with the Memo Function, as well your desired

length and temperature. Then every cup in the future will be customised exactly to your taste. You'll never have to remind it again, unlike the local barista.

## Automatic Milk Frother



The Automatic Milk Frother will deliver your coffee's crowning glory at the touch of a button. Within seconds it will be topped with a silky, milk layer of the finest consistency – the ultimate lure for all cappuccino lovers.

# Specifications

## Sustainability

Power consumption brewing: 1400 W

## General specifications

Cups at the same time: 2

Suitable for: Whole coffee beans, ground coffee powder

One touch variety: 4

Coffee strength settings: 3

Temperature settings: 3

Grinder settings: 5

Type of display: LCD

Special functions: Ceramic grinder, Pre-brewing, Hot water option, Automatic milk frother

Customizing per drink: Adjustable coffee strength, Adjustable temperature, Adjustable cup volume

Ease of use and comfort: Cup warmer, Display, Removable spout, Removable drip-tray, Automatic stand-by, Automatic shut-off

Ease of cleaning & maintenance: Automatic de-scaling cycle, Removable brewing group, Steam cleaning, Automatic rinse cycle

Coffee drinks: Espresso, Cappuccino, hot water, Café Crème, frothed milk, Espresso Macchiato, Latte Macchiato

## Finishing

Material boiler: Stainless steel (Inox)

Material drip tray: Stainless steel

Material of main body: Stainless steel & plastic

Material water tank: Plastic

## Service

2-year guarantee

## Technical specifications

Pump pressure: 15 bar

Capacity bean container: 350 gr

Capacity waste container: 20 servings

Max. cup height: 100 mm

Brewing time one cup: 45 (espresso) to 100 (long coffee) sec

Water boilers: 2

Cord length: 0.8 m

Capacity water tank: 2.2 L

Frequency: 50 Hz

Voltage: 230 V

## Weight and dimensions

Weight of product: 15 kg

Dimensions of product (WxDxH): 336 x 380 x 450 mm

## Design

Color: Silver

## Country of origin

Made in: Italy

