

# PHILIPS

## Saeco

Super-automatic  
espresso machine

Royal

Brews 7 coffee varieties

Automatic Milk Frother

Silver

5-step adjustable grinder

HD8930/01



## Solid performance, cup after cup

With large-capacity containers

The new Saeco Royal espresso machine is the rejuvenation of a trusted classic. What remains unchanged is the extremely solid performance and the generous tanks for beans, water and coffee grounds.

### Authentic Italian coffee perfection

- Delicious milk froth thanks to the automatic milk frother
- Milk specialities without the wait thanks to a double boiler

### Set the beverages to suit your taste

- Save your favourite coffee settings
- Avoid heat loss and fit every cup with our adjustable spout

### Easy to clean and maintain

- Always a clean machine thanks to auto-clean and descaling
- Easy cleaning thanks to removable brewing group
- Easy cleaning thanks to dishwasher-safe parts

# Highlights

## Saves your coffee settings



You will always get a perfect cup of espresso brewed just for you, according to your personal preference, thanks to our innovative memo function for adjusting the coffee length, strength and temperature. Enjoy a superb coffee drink in your favourite cup at the touch of a button.

## Adjustable spout



The adjustable spout on our espresso machines will fit every cup and thus prevent the coffee splashing or cooling down while being poured into your cup. This way your espresso is always served at the right temperature, while the machine is kept clean.

## Dishwasher-safe parts



For your convenience, you can put the Saeco's drip tray and milk frother or milk carafe in the dishwasher. This will save time and ensure a hygienic clean.

## Removable brewing group



The brewing group, a Saeco invention, is the heart of our espresso machines, ensuring automation. The brewing group is, depending on the model, easily accessible from the front or side. It can be removed effortlessly for easy cleaning by rinsing under the tap, ensuring maximum hygiene.

## Auto-cleaning and descaling



Saeco designed this espresso machine to automatically clean its coffee circuit with water when starting up or switching off to deliver a great, fresh taste with each cup of coffee.

Regular descaling prolongs your espresso machine's life. This machine will not only prompt when descaling is needed, the automated descaling process will start and guide you with clear on-screen messages when you have to intervene. Descaling has never been so easy!

## Automatic milk frother



Preparing a tasty cappuccino is easy with this Saeco espresso machine thanks to the automatic milk frother, which baristas also call "cappuccinatore". The milk frother will draw milk directly from a milk carton or jug and froth it automatically, dispensing it directly into your cup. With just one touch you will instantly get a delicious and creamy froth.

## Professional double boiler



With 2 separate heating systems to cater for both the optimal coffee temperature and the milk frothing temperature, this Saeco fully automatic espresso machine guarantees professional performance and speed every time. You are able to prepare as many latte macchiatos and cappuccinos as you wish, one after the other and each just as good as the previous one, without waiting.

# Specifications

## Service

2-year worldwide guarantee

## Perfect Espresso

Espresso technology: Aroma-system: pre-brewing, Cup warmer

## Technical specifications

**Water pressure in pump:** 15 bar (perfect espresso)

**Supported coffee types:** Ground coffee, Whole coffee beans

**Country of origin:** Made in Italy, Designed in Italy

**Removable brewing group**

**Cord length:** 80 cm

**Number of water boilers:** 2 boilers (instant steam)

**Frequency:** 50 Hz

**Power:** 1400 W

**Voltage:** 230 V

**Boiler material:** Stainless steel (Inox)

## Easy to use

**Cleaning and maintenance:** Automatic milk circuit rinse, Descaling cycle

**Usage:** Adjustable coffee dispenser, Instant steam (2 boilers), Removable brewing group

## Weight and dimensions

**Product weight:** 15 kg

**Product dimensions (L x D x H):** 336 x 380 x 450 mm

**Coffee bean capacity:** 350 gr

**Waste container capacity:** 20 servings

**Water tank capacity:** 2.2 l

**Maximum cup height:** 100 mm

## Features

Simultaneous brewing

Hot water wand

## Design

**Colour:** Glossy Silver

**Materials and finishing:** Plastic Front/Top + Metal sides/rear

## Energy saving

**Energy saving:** Automatic stand-by

## Country of origin

Made in: Italy

