

# PHILIPS

## Saeco

Super-automatic  
espresso machine

Royal

Royal

One Touch

HD8930/02



## Solid performance cup after cup

With large capacities and an insulated milk container

The new Saeco Royal is the rejuvenation of a trusted classic. What remains unchanged is the extremely solid performance and the generous tanks for beans, water and coffee grounds.

### Easy to use

- Cup warmer
- Ergonomic in day to day operation
- Insulated milk container
- One touch beverage selection

### Easy to clean and maintain

- Always a clean machine thanks to auto-clean and descaling
- Dishwasher safe Cappuccinatore
- Easy cleaning stainless steel milk container

### Coffee speciality customisation

- Adjustable coffee length and intensity

### High performance all day long

- Large capacity containers
- Milk specialities without the wait thanks to a double boiler

# Highlights

## Adjustable coffee length and



Choose your favourite coffee blend and adjust the coffee length and intensity (temperature, pre-brewing, strength). Length: you can adjust the amount of brewed coffee according to your taste and/or the size of your cups. Temperature: the machine allows you to adjust the temperature of your coffee via the settings menu. Pre-brewing: via the settings menu you can adjust the time for pre-wetting the coffee powder in the infusion chamber, in order to extract all the taste. Strength: the machine is set up to adjust the strength with the amount of coffee to be ground, using the specific lever on the side.

## Auto-cleaning and descaling




Saeco designed this espresso machine to automatically clean its coffee circuit with water when starting up or switching off to deliver a great, fresh taste with each cup of coffee. Regular descaling prolongs your espresso machine's life. This machine will not only prompt when descaling is needed, the automated descaling process will start and guide you with clear on-screen messages when you have to intervene. Descaling has never been so easy!

## Cup warmer



This feature allows you to not only store your espresso cups and glasses right on the espresso machine, it also pre-heats them letting the aroma unfold even better and guaranteeing a long-lasting crema

## Dishwasher safe Cappuccinatore



Keep the Saeco espresso machine at its best by cleaning the automatic Cappuccinatore. Simply wash it with lukewarm water or put it straight in the dishwasher.

## Professional double boiler



With 2 separate heating systems to cater for both the optimal coffee temperature and the milk frothing temperature, this Saeco fully automatic espresso machine guarantees professional performance and speed every time. You are able to prepare as many latte

macchiatos and cappuccinos as you wish, one after the other and each just as good as the previous one, without waiting.

## Easy cleaning milk container



Easy cleaning stainless steel milk container

## Ergonomic day to day



Saeco is a synonym for convenience: refilling beans or water, emptying the coffee-dump box or the drip tray, all compartments of the full automatic coffee machine are directly accessible.

## Insulated milk container



Insulated milk container

# Specifications

## Technical specifications

**Boiler material:** Stainless steel (Inox)

**Country of origin:** Made in Italy, Designed in Italy

**Power:** 1400 W

**Voltage:** 230 V

**Frequency:** 50 Hz

**Cord length:** 80 cm

## Sustainability

Automatic Standby Option

## Perfect Espresso

**Espresso technology:** Aroma-system: pre-brewing, Cup warmer

## Easy to use

**Cleaning and maintenance:** Automatic milk circuit rinse, Descaling cycle

**Usage:** Adjustable coffee dispenser, Instant steam (2 boilers), Removable brewing group

## Weight and dimensions

**Product weight:** 15 kg

**Product dimensions (L x D x H):** 336 x 380 x 450 mm

**Coffee bean capacity:** 350 gr

**Waste container capacity:** 20 servings

**Milk carafe capacity:** 0.5 l

**Water tank capacity:** 2.2 l

## Features

Simultaneous brewing

Hot water wand

## Design

**Colour:** Glossy Silver

**Materials and finishing:** Plastic Front/Top + Metal sides/rear

